



108065822 | M61A-318

M61 Information Outlet Icon Insert for MGS Information Outlet, blue

## Environmental Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Flammability Rating   | UL 94 V-0                            |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Safety Standard       | cUL   UL                             |
| Storage Temperature   | -40 °C to +70 °C (-40 °F to +158 °F) |

## General Specifications

|                  |      |
|------------------|------|
| Product Type     | Icon |
| Color            | Blue |
| Package Quantity | 25   |

## Mechanical Specifications

|               |                                             |
|---------------|---------------------------------------------|
| Material Type | High-impact, flame retardant, thermoplastic |
|---------------|---------------------------------------------|

## Regulatory Compliance/Certifications

| Agency          | Classification                                                                 |
|-----------------|--------------------------------------------------------------------------------|
| RoHS 2011/65/EU | Compliant                                                                      |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |

