



760018820 | 6 FIBER BREAKOUT KIT  
6 Fiber Breakout Kit, loose tube

## Construction Materials

Material Type, body	ABS plastic
Material Type, tubing	Thermoplastic elastomer (TPE)

## Dimensions

Height	7.62 mm   0.30 in
Length	43.18 mm   1.70 in
Tube Inner Diameter	500.00 µm
Tube Length	609.6 mm   24.0 in
Tube Outer Diameter	900.00 µm
Width	17.78 mm   0.70 in

## Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
-----------------------	--------------------------------------

## General Specifications

Product Type	Breakout kit
Color	Black
Compatible Interface	LC   LC, keyed   SC   ST
Includes	Breakout unit   Instruction sheet   Six buffer tubes, 24 in x 900 µm   Snap together housing
Package Quantity	1

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

