



760018838 | 12 FIBER BREAKOUT KIT  
12 Fiber Breakout Kit, loose tube

## Construction Materials

|                       |                               |
|-----------------------|-------------------------------|
| Material Type, body   | ABS plastic                   |
| Material Type, tubing | Thermoplastic elastomer (TPE) |

## Dimensions

|                     |                    |
|---------------------|--------------------|
| Height              | 7.62 mm   0.30 in  |
| Length              | 43.18 mm   1.70 in |
| Tube Inner Diameter | 500.00 µm          |
| Tube Length         | 609.6 mm   24.0 in |
| Tube Outer Diameter | 900.00 µm          |
| Width               | 17.78 mm   0.70 in |

## Environmental Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
|-----------------------|--------------------------------------|

## General Specifications

|                      |                                                                                                 |
|----------------------|-------------------------------------------------------------------------------------------------|
| Product Type         | Breakout kit                                                                                    |
| Color                | Black                                                                                           |
| Compatible Interface | LC   LC, keyed   SC   ST                                                                        |
| Includes             | Breakout unit   Instruction sheet   Snap together housing   Twelve buffer tubes, 24 in x 900 µm |
| Package Quantity     | 1                                                                                               |

## Regulatory Compliance/Certifications

|                 |                                                                                |
|-----------------|--------------------------------------------------------------------------------|
| <b>Agency</b>   | <b>Classification</b>                                                          |
| RoHS 2011/65/EU | Compliant                                                                      |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |

