



760031716 | iP-POWER-SUPPLY
iPatch® Power Supply 12VDC 3050 mm Power Cord

General Specifications

Brand	iPatch® SYSTIMAX®
Product Type	Infrastructure control system
Color	Black
Includes	Five types AC power plugs Power supply, 12 Vdc
Package Quantity	1

Dimensions

Depth	33.02 mm 1.30 in
Height	71.12 mm 2.80 in
Width	43.18 mm 1.70 in
Weight	0.23 kg 0.50 lb

Mechanical Specifications

Material Type	Polycarbonate
---------------	---------------

Electrical Specifications

Input Voltage	100–240 Vac
Output Current at Voltage, continuous	1.25 A @ 12 Vdc
Power Frequency	50–60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	ACMA CE cUL GB INNOVA GS PSE UL

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

