

## This specification is OBSOLETE



760039743 | RFE-MOD-012-8W-MPO-LC02

**ReadyPATCH® TeraSPEED® Standard Module, 12 LC ports**

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

## OBSOLETE

This product was discontinued on: March 1, 2013

## Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1   OS2)
Total Fibers, quantity	12

## Dimensions

Depth	127.00 mm   5.00 in
Height	27.94 mm   1.10 in
Width	129.54 mm   5.10 in

## Environmental Specifications

Safety Standard	UL
-----------------	----

## General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	6
Brand	ReadyPATCH®
Data Module Type	Standard
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

## Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	1.15 dB
Return Loss, minimum	55.0 dB

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)