



760073866 | iP-M4200i-24

**iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules**

## Dimensions

Depth	25.40 mm   1.00 in
Height	44.45 mm   1.75 in
Weight	0.68 kg   1.50 lb
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	6   6A
-------------------	--------

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA   CE   cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Product Type	Panel, modular
Brand	iPatch®   SYSTIMAX®
Color	Black
Includes	Cable management bar   Four #12-24 dog point mounting screws   Information outlet removal tool   Instruction sheet   Panel   Two #12 washers   Two #12-24 screws
Package Quantity	1

## Mechanical Specifications

Panel Style	Straight
Material Type	ABS   Polycarbonate

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

