

## This specification is **OBSOLETE**



760092809 | 1100A GS3-2U Panel Kit  
GigaSPEED XL® 1100GS3 Category 6 U/UTP Angled 2U Panel Kit

### **OBSOLETE**

This product was discontinued on: **December 1, 2015**

#### Replaced By:

760206920 1100 ANGLED GS3 PANEL KIT - 2U  
1100A-U-GS3-KIT-2U

## Dimensions

Depth	40.64 mm   1.60 in
Height	95.25 mm   3.75 in
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	6
-------------------	---

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	Passive
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	GigaSPEED XL®   SYSTIMAX®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2

## Mechanical Specifications

Panel Style	Angled
Material Type	Powder-coated steel

## Regulatory Compliance/Certifications

# Product Specifications



760092809 | 1100A GS3-2U Panel Kit

**Agency**

RoHS 2011/65/EU  
ISO 9001:2008

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

