



760093351 | 360-iP-HD-MOD-LC-LS-3
SYSTIMAX 360™ iPatch® G2 LazrSPEED® High Density Module, 3 pack

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber (OM4)
Material Type	ABS Polycarbonate

Dimensions

Depth	215.90 mm 8.50 in
Height	82.55 mm 3.25 in
Width	152.40 mm 6.00 in
Weight	1.13 kg 2.50 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	CE cUL UL ACMA
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Product Type	Shelf
Interface, front	LC
Total Ports, quantity, front	144
Interface Feature, front	Standard
Color, front	Aqua
Brand	SYSTIMAX 360™ SYSTIMAX® iPatch®
Color	Black
Intelligence Type	iPatch® enabled
Interface, rear	MPO
Adapters, quantity, rear	12
Interface Feature, rear	Reduced footprint
Color, rear	Black
Package Quantity	3

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.50 dB
Return Loss, minimum	20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)