



760105429 | M4800-1U-GS

**M4800 1U Modular Panel, 48 port, for SYSTIMAX Category 6A and 6 Information Outlets and Uniprise Category 6A Information Outlets**

- Available for use with the DYMO® labeling solution

## Dimensions

Depth	53.85 mm		2.12 in
Height	44.45 mm		1.75 in
Width	482.60 mm		19.00 in

## Electrical Specifications

ANSI/TIA Category	6		6A
-------------------	---	--	----

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	Passive
Product Type	Panel, modular
Brand	CommScope®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

## Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic		Steel
---------------	---	--	-------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

