

760105445 | MGS-CAP-50  
MGS Cap Kit - LP (Pack of 50)



## Electrical Specifications

ANSI/TIA Category 6 | 6A

## Environmental Specifications

Flammability Rating UL 94 V-0  
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)  
Relative Humidity Up to 95%, non-condensing  
Safety Standard cUL | UL  
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Product Type Cap  
Brand GigaSPEED X10D® | GigaSPEED XL® | SYSTEMAX®  
Color Gray  
Package Quantity 50

## Mechanical Specifications

Material Type High-impact, flame retardant, thermoplastic

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

