



760109488 | 360G2 Cartridge 12-LC-MM-BG-Pigtails
360G2 Cartridge 12 LC OptiSPEED® Beige with Pigtails iPatch Ready

Construction Materials

Fiber Type	OptiSPEED®, 62.5 µm multimode fiber (OM1)
Total Fibers, quantity	12

Dimensions

Depth	119.38 mm 4.70 in
Height	30.48 mm 1.20 in
Pigtail Length	1.5 m 4.9 ft
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Brand	SYSTIMAX 360™ SYSTIMAX®
Product Type	Cartridge
Interface, front	LC
Adapter Color	Beige
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	12

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, typical	0.20 dB
Return Loss, minimum	20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

- 860278498 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, blue, 1.5 m
- 760099317 | X-TB-6F-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278506 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, orange, 1.5 m
- 760099325 | X-TB-6F-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278514 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, green, 1.5 m
- 760099333 | X-TB-6F-GR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278522 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, brown, 1.5 m
- 760099341 | X-TB-6F-BR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278530 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, slate, 1.5 m
- 760038562 | X-TB-6F-SL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278548 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, white, 1.5 m
- 760099358 | X-TB-6F-WH-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278555 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, red, 1.5 m
- 760099366 | X-TB-6F-RD-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278563 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, black, 1.5 m
- 760099374 | X-TB-6F-BK-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278571 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, yellow, 1.5 m
- 760099382 | X-TB-6F-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- 860278589 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, violet, 1.5 m
- 760099390 | X-TB-6F-VI-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
 - 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

760109488 | 360G2 Cartridge 12-LC-MM-BG-Pigtails

860278597 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, rose, 1.5 m

- 760099408 | X-TB-6F-RS-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

860278605 (Product Component—not orderable) — OptiSPEED® LC 0.9 mm Pigtail, aqua, 1.5 m

- 760099416 | X-TB-6F-AQ-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode

700206949 | MFA-LC12-BG-SHUTTERED — OptiSPEED® LC Multiport Shuttered Adapter, Beige, Single Pack

* Footnotes

Insertion Loss Change, mating Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)