

760109629 | 360G2 Cartridge 6-ST-MM-BG-Pigtails A  
360G2 Cartridge 6 ST OptiSPEED® Beige with Pigtails A



## Construction Materials

Fiber Type	OptiSPEED®, 62.5 µm multimode fiber (OM1)
Total Fibers, quantity	6

## Dimensions

Depth	119.38 mm   4.70 in
Height	30.48 mm   1.20 in
Pigtail Length	1.5 m   4.9 ft
Width	91.44 mm   3.60 in

## Environmental Specifications

Safety Standard	UL
-----------------	----

## General Specifications

Brand	SYSTIMAX 360™   SYSTIMAX®
Product Type	Cartridge
Interface, front	ST
Adapter Color	Beige
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	6

## Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, typical	0.30 dB
Return Loss, minimum	20.0 dB

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

- 860279215 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, blue, 1.5 m
- 760099317 | X-TB-6F-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 860279223 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, orange, 1.5 m
- 760099325 | X-TB-6F-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 860279231 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, green, 1.5 m
- 760099333 | X-TB-6F-GR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 860279249 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, brown, 1.5 m
- 760099341 | X-TB-6F-BR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 860279256 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, slate, 1.5 m
- 760038562 | X-TB-6F-SL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 860279264 (Product Component—not orderable) — OptiSPEED® ST 0.9 mm Pigtail, white, 1.5 m
- 760099358 | X-TB-6F-WH-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
  - 700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode
- 700206964 | MFA-ST06-BG-SHUTTERED — OptiSPEED® ST Multiport Shuttered Adapter, Beige, Single Pack

## \* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)