



760109892 | 360DM-24LC-TS

InstaPATCH® 360 TeraSPEED® Standard Module, 24 LC ports

Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Total Fibers, quantity	24

Dimensions

Depth	116.84 mm 4.60 in
Height	30.48 mm 1.20 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	12
Brand	InstaPATCH® 360
Data Module Type	Standard
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	2
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	1.15 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)