

**760118349 | M2400A-1U-GS****CommScope® U/UTP Angled Single-Row Modular Panel, 24 port (MGS400/500/600)**

## Dimensions

Depth	138.18 mm		5.44 in
Diameter Over Dielectric, maximum	1.168 mm		0.046 in
Diameter Over Dielectric, minimum	0.762 mm		0.030 in
Height	43.69 mm		1.72 in
Width	482.60 mm		19.00 in

## Electrical Specifications

ANSI/TIA Category	6		6A
-------------------	---	--	----

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	Passive
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Product Type	Panel, modular
Brand	CommScope®   GigaSPEED X10D®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

## Mechanical Specifications

Panel Style	Angled
Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

