



760154237 | HGS-A-MS-GREEN  
High Density M-Series Adapter, green

## Dimensions

Depth	9.14 mm   0.36 in
Height	17.53 mm   0.69 in
Width	18.54 mm   0.73 in

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Product Type	Adapter
Color	Green
Brand	SYSTIMAX®
Ordering Note	Minimum order quantity, 20 packs
Package Quantity	25

## Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

