



760160507 | IPQ-IPR-1U-24P
InstaPATCH® QUATTRO Modular Panel, 1U, 24 port

Dimensions

Depth	87.63 mm 3.45 in
Depth, with cable management	3.00 in
Height	43.94 mm 1.73 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1000 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® ready
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Product Type	Panel, modular
Brand	InstaPATCH® QUATTRO
Color	Cool gray
Includes	Label sheet
Label Height	0.33 in
Label Length	16.77 in
Modules, quantity	6
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

Mechanical Specifications

Panel Style	Straight
Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug

760160507 | IPQ4PR-1U-24P

Plug Retention Force, minimum	133 N 30 lbf
Rear Termination Contact Plating	Nickel
Rear Termination Type	MC Female

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

