



760206532 | 360DMis-24LC-LS  
**InstaPATCH® 360 LazrSpeed® Standard Module, 24 LC Ports**

## Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber (OM4)
Total Fibers, quantity	24

## Dimensions

Depth	116.84 mm   4.60 in
Height	27.94 mm   1.10 in
Width	91.44 mm   3.60 in

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Aqua
Interface, rear	MPO
Adapters, quantity, rear	2
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

## Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.50 dB
Return Loss, minimum	27.0 dB

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2008	

### \* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)