

N-STYLE BULKHEAD JACK TO PLUG LIGHTNING ARRESTOR



The AccelTex Solutions bi-directional gas discharge tube lightning arrestor protects outdoor equipment from the buildup and discharge of static electricity that affects the operation and lifespan of your network.

Part Number: ATS-LP-N-BHJ-P

> ELECTRICAL SPECIFICATIONS

Impedance: 50 Ω

Frequency Range: DC-5.85 GHz

Discharge Voltage: 90V

VSWR: ≤ 1.3

Insertion Loss: ≤ 0.2 dB

Center Conductor Contact Resistance: ≤ 1 m Ω

Outer Conductor Contact Resistance: ≤ 1 m Ω

Dielectric Withstand: 2500V RMS

Insulation Resistance: ≥ 1000 M Ω

> MECHANICAL SPECIFICATIONS

Connector 1 Style: N-Style Bulkhead Jack

Connector 2 Style: N-Style Plug

Mating: 5/8 -24UNEF-2A and 5/8-24UNEF-2B

Durability: ≥ 500 Cycles

Installation: DIN Rail Mount and L Bracket

Body: Nickel Plated Brass

Insulator: Teflon

Contact Socket: Gold Plated Phosphor Bronze

Contact Pin: Gold Plated Brass

> ENVIRONMENTAL SPECIFICATIONS

Operating Temperature: -40 to 185°F (-40 to 85°C)

> STANDARDS, TESTING AND CERTIFICATIONS

IEC 60169-16

ROHS 2011/65/EU Compliant

> WARRANTY

1 Year Limited Warranty