RPTNC BULKHEAD JACK TO PLUG LIGHTNING ARRESTOR

The AccelTex Solutions bi-directional gas discharge tube lightning arrestor protects outdoor equipment from the buildup and discharge of static electricity that affects the operation and lifespan of your network.

Part Number: ATS-LP-RPTNC-BHJ-P

> ELECTRICAL SPECIFICATIONS

Impedance: 50Ω
Frequency Range: DC-5.85 GHz
Discharge Voltage: 90V
VSWR: ≤1.7
Insertion Loss: ≤0.3dB

Center Conductor Contact Resistance: ≤ 10mΩ
Outer Conductor Contact Resistance: ≤ 2.5mΩ
Dielectric Withstand: 1500V RMS
Insulation Resistance: ≥ 5000MΩ

> MECHANICAL SPECIFICATIONS

Connector 1 Style: RPTNC Bulkhead Jack
Connector 2 Style: RPTNC Plug
Mating: 7/16-28UNEF-2A and 7/16-28UNEF-2B
Durability: ≥ 500 Cycles
Installation: DIN Rail Mount and L Bracket

Body: Nickel Plated Brass
Insulator: Teflon
Contact Socket: Gold Plated Bronze
Contact Pin: Gold Plated Bronze

> ENVIRONMENTAL SPECIFICATIONS

Operating Temperature: -40 to 185°F (-40 to 85°C)

> STANDARDS, TESTING AND CERTIFICATIONS

IEC 60169-17
ROHS 2011/65/EU Compliant

> WARRANTY

1 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2014 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906
SALES@ACCELTEX.COM