

Part Number: 9154

Single-Pair, (1 pr) 20 AWG (7x28) TC, PVC/PVC, Foil

Shld, CMG

Product Description

One 20 AWG pair stranded (7x28) tinned copper conductors, twisted pair, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

Insulation:

AWG	Stranding	Material	No. of Pairs
20	7×28	TC - Tinned Copper	1

Total Number of Conductors:

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

Color Chart 1:

Number	Color
1	Black & Red

Outershield 1:

Туре	• Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil® (Z-Fold®)	100 %	TC - Tinned Copper	22	7x30 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.198 in	0.031 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	11.4 Ohm/1000ft

Capacitance:

No	om. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
60	pF/ft	100 pF/ft

Impedance:

Nominal Characteristic Impedance 36 Ohm

Current:

Max. Recomme	ded Current [A]	
4 Amps per cond	ctor @ 25°C	

Inductance:

Nominal Inductance		
0.18 μH/ft		

Voltage:

UL Voltage Rating		
300 V RMS		

Use

Max Recommended Pulling Tension:	39 lbs

Safety

CSA Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading

Temperature Range

Operating Temp Range:	-20°C To +80°C
UL Temp Rating:	80°C (UL AWM Style 2464)

Mechanical Characteristics

Min Bend Radius/Minor Axis:	2 in	
-----------------------------	------	--

Part Number

Plenum (Y/N):	No

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)	
CEC/C(UL) Specification:	CEC/C(UL) Specification	
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)	
NEC/(UL) Specification:	NEC/(UL) Specification	
UL AWM Style:	AWM Specification	
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)	
EU CE Mark:	EU CE Mark	

History

Product Variants

Part Number	Color	Put-Up Type	Length
9154 2901000	BEIGE, LIGHT	Reel	1000 ft
9154 2905000	BEIGE, LIGHT	Reel	5000 ft
9154 290500	BEIGE, LIGHT	Reel	500 ft
9154 290U1000	BEIGE, LIGHT	UnReel	1000 ft
9154 290U500	BEIGE, LIGHT	UnReel	500 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will, Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor?s inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden?s knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product listelf or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

 $Belden\ declares\ this\ product\ to\ be\ in\ compliance\ with\ EU\ LVD\ (Low\ Voltage\ Directive\ 73/23/EEC),\ as\ amended\ by\ directive\ 93/68/EEC.$