

Part Number: 39114

Hook-Up/Lead Wire PPO, 600V, 105°C AWM Style
11032, (1) 14 AWG (41x30) TC, PPO, 600V, 105°C

Product Description

One 14 AWG stranded (41x30) tinned copper conductor, polyphenylene oxide (PPO) insulation.

Product Specifications

Technical Specifications

Suitable Applications:	Electrical panel builders, Electrical/electronic manufacturers, Appliance manufacturers, Furniture, Computer manufacturers, Automotive companies and their sub-suppliers
-------------------------------	--

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors
14	41x30	TC - Tinned Copper	1
Total Number of Conductors:			1

Insulation:

Material	Nominal Wall Thickness
PPO - Polyphenylene Oxide	0.012 in

Stranding:

Lay Length
AWM 110±8 mm

Outerjacket 1:

Nominal Diameter
0.097 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR

2.35 Ohm/1000ft

Current:

Element	Max. Recommended Current [A]
Single conductor in free air @ 30C ambient	39 amps

Voltage:

UL Voltage Rating
600 Vac

Use

Safety

UL Flammability:	VW-1
------------------	------

Temperature Range

Operating Temp Range:	-40°C To +105°C Dry
-----------------------	---------------------

Mechanical Characteristics

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
UL AWM Style:	UL Style
UL Rating:	UL Rating
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Notes:	Halogen-free.
--------	---------------

Product Variants

Part Number	Color	Put-Up Type	Length
39114 0011000	BROWN	Reel	1000 ft
39114 001100	BROWN	Reel	100 ft
39114 0015000	BROWN	Reel	5000 ft
39114 0021000	RED	Reel	1000 ft
39114 002100	RED	Reel	100 ft
39114 0025000	RED	Reel	5000 ft
39114 0031000	ORANGE	Reel	1000 ft
39114 003100	ORANGE	Reel	100 ft
39114 0035000	ORANGE	Reel	5000 ft
39114 0041000	YELLOW	Reel	1000 ft
39114 004100	YELLOW	Reel	100 ft
39114 0045000	YELLOW	Reel	5000 ft
39114 0051000	GREEN, DARK	Reel	1000 ft
39114 005100	GREEN, DARK	Reel	100 ft
39114 0055000	GREEN, DARK	Reel	5000 ft
39114 0071000	VIOLET	Reel	1000 ft
39114 007100	VIOLET	Reel	100 ft
39114 0075000	VIOLET	Reel	5000 ft
39114 0081000	GRAY	Reel	1000 ft
39114 008100	GRAY	Reel	100 ft
39114 0085000	GRAY	Reel	5000 ft
39114 0091000	WHITE	Reel	1000 ft
39114 009100	WHITE	Reel	100 ft
39114 0095000	WHITE	Reel	5000 ft
39114 0101000	BLACK	Reel	1000 ft
39114 010100	BLACK	Reel	100 ft
39114 0105000	BLACK	Reel	5000 ft
39114 0131000	BLUE, DARK	Reel	1000 ft
39114 013100	BLUE, DARK	Reel	100 ft
39114 0135000	BLUE, DARK	Reel	5000 ft
39114 1891000	GREEN, YELLOW STRIPE	Reel	1000 ft
39114 189100	GREEN, YELLOW STRIPE	Reel	100 ft
39114 1895000	GREEN, YELLOW STRIPE	Reel	5000 ft

© 2016 Belden, Inc.

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.