

Part Number: 83046

Hook-Up/Lead Wire UL AWM Style 1371, (1) 26 AWG
(7x34) SPC, TFE, 105°C

Product Description

One 26 AWG stranded (7x34) silver plated copper conductor, TFE insulation.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors
26	7x34	SPC - Silver Plated Copper	1

Total Number of Conductors:	1
------------------------------------	---

Insulation:

Material	Nominal Wall Thickness
TFE - Tetrafluoroethylene	0.006 in

Outerjacket 1:

Nominal Diameter
0.031 in

Electrical Characteristics

Use

Safety

UL Flammability:	VW-1
-------------------------	------

Temperature Range

Mechanical Characteristics

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
MIL Spec Rating:	MIL Spec Rating
Military Specification:	Military Specification
UL Rating:	UL Rating
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Product Variants

Part Number	Color	Put-Up Type	Length
83046 0011000	BROWN	Reel	1000 ft
83046 0021000	RED	Reel	1000 ft
83046 0031000	ORANGE	Reel	1000 ft
83046 0041000	YELLOW	Reel	1000 ft
83046 0061000	BLUE, LIGHT	Reel	1000 ft
83046 006100	BLUE, LIGHT	Reel	100 ft
83046 0071000	VIOLET	Reel	1000 ft
83046 007100	VIOLET	Reel	100 ft
83046 0091000	WHITE	Reel	1000 ft
83046 009100	WHITE	Reel	100 ft
83046 0101000	BLACK	Reel	1000 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.