



KRAMER

BCP-5X-SOLID

Bulk 5 Mini Coax High-Resolution Solid Core Cable - Plenum Rated



Kramer's **BCP-5X-SOLID** is a plenum rated high resolution 5-coax cable typically used for routing RGBHV signals in professional AV systems. It is optimized for use with a new generation of one piece compression connectors. It offers the best possible precision and ease of use in the field when working with BNCs and RCAs. In addition, the solid center conductor is ideal for connecting directly to equipment with terminal blocks.

FEATURES

- **Plenum Rated** - The low smoke and fire resistant properties of plenum rated cable allow it to reside in air return spaces of ceilings, floors, and walls, often saving the cost of installing conduit.
- **Quality Construction** - Each mini coax is a precision system consisting of a solid 25AWG center conductor and foamed FEP dielectric surrounded by aluminum Mylar foil and tinned copper spiral shields. A white stripe in the jacket makes it easy to distinguish from its stranded counterpart.
- **Numerous Applications** - The most common application is routing RGBHV signals in pro AV systems but BCP-5X-SOLID also offers excellent performance with any combination of component or composite video, and/or unbalanced audio.
- **New Generation One-Piece Connectors** - For quickest assembly use Kramer linear compression and stripper coax tools.
- **Varied Selection of Length** - Available in reels of 76/152/304m (250/500/1000ft).