



Our smallest and most lightweight handheld tactical flashlights produce a lot of light and feature TEN-TAP® Programming. From super-compact, single battery models to models that use two batteries, these everyday carry lights meet all your lighting needs.

Single-Battery Models	Two-Battery Models
<p>ProTac® 1L #88030</p> <ul style="list-style-type: none"> - High: 180 lumens; 3,800 candela; 123m beam; runs 2 hours - Low: 12 lumens; 250 candela; 32m beam; runs 24 hours - Strobe runs 4 hours - Uses one 3V CR123A lithium battery (included) - 3.43" (8.71 cm); 2 oz (57 grams) 	<p>ProTac® 2L #88031</p> <ul style="list-style-type: none"> - High: 260 lumens; 5,600 candela; 150m beam; runs 3 hours - Low: 13 lumens; 300 candela; 35m beam; runs 50 hours - Strobe runs 6 hours - Uses two 3V CR123A lithium batteries (included) - 4.77" (12.12 cm); 2.8 oz (79 grams) 
<p>ProTac® 1AA #88032</p> <ul style="list-style-type: none"> - High: 70 lumens; 1,450 candela; 76m beam; runs 2 hours - Low: 5 lumens; 125 candela; 22m beam; runs 32 hours - Strobe runs 4 hours - Uses 1 "AA" alkaline battery (included) - Also accepts 1 "AA" lithium battery for extended run time - 4.16" (10.57 cm); 2.3 oz (65 grams) 	<p>ProTac® 2AA #88033</p> <ul style="list-style-type: none"> - High: 155 lumens; 3,300 candela; 115m beam; runs 2 hours - Low: 5 lumens; 125 candela; 22m beam; runs 32 hours - Strobe runs 4 hours - Uses 2 "AA" alkaline batteries (included) - 6.14" (15.6 cm); 3.4 oz (96 grams) 
<p>ProTac® 1AAA #88049</p> <ul style="list-style-type: none"> - High: 70 lumens; 550 candela; 47m beam; runs 30 minutes (alkaline); 2.25 hours (lithium) - Low: 5 lumens; 40 candela; 13m beam; runs 11 hours (alkaline); 22 hours (lithium) - Strobe runs 1.2 hours (alkaline); 5 hours (lithium) - Uses 1 "AAA" alkaline battery (included) - Also accepts 1 "AAA" lithium battery for extended run time - 3.94" (10 cm); 1.3 oz (37 grams) 	<p>ProTac® 2AAA #88039</p> <ul style="list-style-type: none"> - High: 80 lumens; 1,550 candela; 80m beam; runs 1.5 hours - Low: 10 lumens; 200 candela; 28m beam; runs 30 hours - Strobe runs 5 hours - Uses 2 "AAA" alkaline batteries (included) - 5.62" (14.27 cm); 2 oz (57 grams) <p><i>Does not feature TEN TAP Programming</i></p> 
<p>Common Features:</p> <ul style="list-style-type: none"> - C4® LED technology for extreme brightness - Solid State power regulation provides maximum light output throughout battery life - Durable, anodized aluminum construction with o-ring sealed glass lens - IPX7 waterproof to 1 meter for 30 minutes - 2 meter impact resistance tested <ul style="list-style-type: none"> - TEN-TAP® Programmable switch allows user to select one of three different programmed lighting modes - Anti-roll facecap - Removable pocket clip - Includes nylon holster 	