

You asked, we listened! The redesigned Survivor features a low-profile bezel that doesn't interfere with gear and equipment. We also redesigned the clip and added a reinforced D-ring so your light hangs forward consistently.



Custom designed optic with optional, interchangeable Smoke-Cutter® plugs for preferred beam pattern:

- Black plug significantly reduces peripheral light for a tighter beam
- Amber plug reduces peripheral light and eye fatigue caused by glare



Strong spring-loaded clip securely grabs onto belts and gear; D-ring features forward hanging orientation

Rubber dome push-button switch easy to use with gloves

Rugged nylon polymer body is virtually indestructible

No tools needed to change batteries

Low-profile design doesn't interfere with gear and equipment

New optic combines low profile with strong performance and a wider beam

Dual power source:
Rechargeable NiCd battery; also accepts 4 "AA" alkaline batteries



C4® LED with high, low, emergency flash and moonlight modes

- High for a super-bright beam that pierces through smoke: 41,000 candela; 175 lumens; 405m beam distance; runs 3.5 hours (NiCd); runs 4 hours (alkaline)
- Low for bright light and longer run time: 14,000 candela; 60 lumens; 237m beam distance; runs 13 hours (NiCd); runs 15 hours (alkaline)
- Flash for signaling: runs 8 hours
- Moonlight mode provides low-level lighting for battery conservation: runs 20 days

Optimized electronics provide regulated intensity

"Total Internal Reflection" optic for narrow beam and optimum peripheral illumination

Class I, II, Division 1, Groups C, D, E, F, G; Class III, T-Code: T4
Class I, Division 2, Groups A, B, C, D; T-Code: T4

Rack meets requirements of NFPA 1901-14.1.11.2 (2009) mounted in any position

IPX4 water-resistant; 2 meter impact resistance tested

7.6 in. (17.92 cm); NiCd: 18 oz. (50810 g); Alkaline: 13.17 oz. (37188 g)

Limited Lifetime Warranty

Visit www.streamlight.com for full warranty information

See reverse for item numbers

90515	Survivor with Charger/Holder and 230V AC & 12V DC cords - Yellow
90516	Survivor with Charger/Holder and 240V AC & 12V DC cords - Yellow
90513	Survivor with Charger/Holder and 120V AC & 12V DC cords - Yellow
90517	Survivor with Charger/Holder and 100 AC & 12V DC cords - Yellow
90505	Survivor with Charger/Holder and 230V AC & 12V DC cords - Orange
90506	Survivor with Charger/Holder and 240V AC & 12V DC cords - Orange
90503	Survivor with Charger/Holder and 120V AC & 12V DC cords - Orange
90507	Survivor with Charger/Holder and 100V AC & 12V DC cords - Orange
90525	Survivor with Charger/Holder and 230V AC & 12V DC cords - Black
90526	Survivor with Charger/Holder and 240V AC & 12V DC cords - Black
90523	Survivor with Charger/Holder and 120V AC & 12V DC cords - Black
90527	Survivor with Charger/Holder and 100V AC & 12V DC cords - Black
90512	Survivor with 120V AC Fast Charge - Yellow
90502	Survivor with 120V AC Fast Charge - Orange
90522	Survivor with 120V AC Fast Charge - Black
90519	Survivor with 12V DC - Yellow
90528	Survivor with 12V DC Fast Charge - Black
90509	Survivor with 12V DC Fast Charge - Orange
90510	Survivor(WITHOUT CHARGER) - Yellow
90500	Survivor (WITHOUT CHARGER) - Orange
90520	Survivor (WITHOUT CHARGER) - Black
90541	Survivor Alkaline Model - Yellow
90540	Survivor Alkaline Model - Orange
90545	Survivor Alkaline Model - Black



STREAMLIGHT



30 Eagleville Road, Eagleville, PA 19403 • 800-523-7488 • 610-631-0600 • Fax: 610-631-0712 • 800-220-7007
www.streamlight.com ©2014 Streamlight, Inc. Survivor 10/14