

The far-reaching beam of the Knucklehead Spot can help you locate hazards or victims from a distance. An articulating head gives firefighters more flexibility when working in situations with changing conditions.



Single parabolic reflector provides a tight beam for long range target illumination

Rubber dome push-button actuator is easy to operate even when wearing heavy gloves

High-impact, super-tough nylon polymer construction for exceptional durability

Dual power source: accepts rechargeable NiCd battery pack or 4 "AA" alkaline batteries



Alkaline battery pack holds 4 "AA" alkaline batteries



Head rotates 360°
Articulates 210°



Powerful magnet adheres to steel surfaces



Spring-loaded clip attaches to turn-out gear for convenient hands-free lighting



4 modes:

- High: 180 lumens; 11,000 candela; 210m beam; runs 3.5 hours
- Low: 55 lumens; 3,300 candela; 115m beam; runs 16 hours
- Moonlight mode runs 20 days
- Flash runs 8 hours

IPX4 water-resistant; 2 meter impact-resistance tested

Removable magnet with 135 lb pull strength features a replaceable rubber boot

Class I, Division 2, Groups A,B,C,D; Class II, Division 2, Groups F,G; Class III, Temp Code: T4/T3C

Charger meets requirements of NFPA 1901-14.1.11.2 (2009) mounted in any position

9.2 in. (23.4 cm); NiCd 23.1 oz (655 grams); Alkaline 18.3 oz (519 grams)

Limited lifetime warranty

Visit www.streamlight.com for full warranty information

- #90758 Knucklehead Div 2 Spot - 230V AC (Type C)/12V DC - Orange
- #90759 Knucklehead Div 2 Spot - 240V AC/12V DC - Orange
- #90760 Knucklehead Div 2 Spot - IEC Type A (100V) AC/12V DC - Orange
- #90757 Knucklehead Div 2 Spot - 120V AC/12V DC - Orange
- #90761 Knucklehead Div 2 Spot - 120V AC Fast Charge - Orange
- #90770 Knucklehead Div 2 Spot - 12V DC Fast Charge - Orange
- #90751 Knucklehead Div 2 Spot (without charger) Orange
- #90744 Knucklehead Div 2 Spot - Alkaline Orange - Blister