





# STRION® LED RECHARGEABLE FLASHLIGHT

| FL 1 STANDARD   | HIGH                 | MEDIUM               | LOW                 |
|---|----------------------|----------------------|---------------------|
|  | <b>260</b><br>LUMENS | <b>130</b><br>LUMENS | <b>65</b><br>LUMENS |
|  | <b>2h</b>            | <b>4h</b>            | <b>7h 30min</b>     |
|  | <b>200m</b>          | <b>141m</b>          | <b>100m</b>         |
|  | <b>10,000cd</b>      | <b>5,000cd</b>       | <b>2,500cd</b>      |

Strobe runs 5.5 hours



Case Material 6000 series machined aircraft aluminum with anodized finish

Dimensions Length: 5.90 in. (14.99 cm) Head Diameter: 1.25 in. (3.18 cm) Head Diameter at Tri-Lobe Anti-Roll Flange: 1.44 in. (3.66 cm) Barrel Diameter: 0.95 in. (2.41 cm)

Weight 5.22 oz (148 grams) with battery

Lens Borofloat high temperature glass lens

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime.

Switch Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

Output/Runtime: Three modes and strobe:

- High for a bright super-bright beam - 260 lumens; 10,000 candela peak beam intensity; 200 meter beam distance; runs 2 hours
- Medium for bright light and longer run times – 130 lumens; 5,000 candela peak beam intensity; 141 meter beam distance; runs 4 hours
- Low for light without glare and extended run times – 65 lumens; 2,500 candela peak beam intensity; 100 meter beam distance; runs 7.5 hours
- Strobe for disorienting or signaling your location; runs 5.5 hours

Battery Lithium Ion with on-board safety control circuit, 3.75V, 2200mAh, rechargeable up to 1000 times

Charging Clamp style charge holder with digital control circuit that prevents over charge. Fully recharges battery in 3 hours. Charge base LED indication: LED Steady – Charging; LED Blinking – Charged. Standard or PiggyBack® charger

- Features
- C4 LED technology for extreme brightness
  - LED Charge-continuity indicator on charger base; Compact, snap-in charger mounts in any position
  - IPX4 water resistant operation; 2 meter impact resistance tested
  - Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

| Description   | Item # | UPC            |
|---|--------|----------------|
| Strion LED with Type C (230V) AC/DC 1 Holder                  | 74311  | 080926-74311-3 |
| Strion LED with 240V AC/DC 1 Holder                           | 74321  | 080926-74321-2 |
| Strion LED with Type A (100V/120V) AC/DC 1 Holder             | 74301  | 080926-74301-4 |
| Strion LED with Type A (100V/120V) AC/DC 1 Holder - Clam      | 74308  | 080926-74308-3 |
| Strion LED with Type C (230V) AC/DC 2 Holders                 | 74312  | 080926-74312-0 |
| Strion LED with 240V AC/DC 2 Holders                          | 74322  | 080926-74322-9 |
| Strion LED with Type A (100V/120V) AC/DC 2 Holders            | 74302  | 080926-74302-1 |
| Strion LED with Type A (100V/120V) AC/DC PiggyBack            | 74353  | 080926-74353-3 |
| Strion LED with Type A (100V/120V) AC/DC PiggyBack - Kryptek® | 74369  | 080926-74369-4 |

Assembled in USA

| Description  | Item # | UPC            |
|--|--------|----------------|
| Strion LED with Type C (230V)                        | 74313  | 080926-74313-7 |
| Strion LED with 240V AC                              | 74323  | 080926-74323-6 |
| Strion LED with Type A (100V/120V) AC                | 74303  | 080926-74303-8 |
| Strion LED with Type A (100V/120V) AC with grip ring | 74303  | 080926-74303-8 |
| Strion LED with DC                                   | 74309  | 080926-74309-0 |
| Strion LED (Without Charger)                         | 74300  | 080926-74300-7 |
| Strion LED (Without Charger) - Kryptek®              | 74368  | 080926-74368-7 |

*Additional part numbers on reverse*

All Rights Reserved. Kryptek® is a registered trademark of Kryptek Outdoor Group, LLC. Streamlight has not sought endorsement of this product from Kryptek Outdoor Group, LLC.





| Item  | UPC              | Part #         |       |
|---|------------------|----------------|-------|
| DC2 direct wire charge cord   | 080926-22050-8   | 22050          |       |
| DC1 Charge Cord   | 080926-22051-5   | 22051          |       |
| 120V AC charge cord   | 080926-22311-0   | 22311          |       |
| IEC Type A (100V & 120V) AC charge cord   | 080926-22060-7   | 22060          |       |
| IEC Type C (230V) AC charge cord  | 080926-22061-4   | 22061          |       |
| 240V AC charge cord   | 080926-22241-0   | 22241          |       |
| USB A to Micro (Custom)   | 080926-22070-6   | 22070          |       |
| 120V AC USB Wall Plug   | 080926-22058-4   | 22058          |       |
| Intl AC USB Wall Plug   | 080926-22059-1   | 22059          |       |
| 6-unit Bank Charger 120V AC   | 080926-74400-4   | 74400          |       |
| 6-unit Bank Charger 230V AC   | 080926-74600-8   | 74600          |       |
| 6-unit Bank Charger 12V DC  | 080926-74401-1   | 74401          |       |
| USB Charger Holder  | 080926-74114-0   | 74114          |       |
| PiggyBack Charger Holder (cords and battery not included)   | 080926-74115-7   | 74115          |       |
| Battery Stick (Li-Ion)  | 080926-74175-1   | 74175          |       |
| Rail Mount  | 080926-74200-0   | 74200          |       |
| Vertical Grip with Rail - machined aluminum, ambidextrous hard anodized rail grabber vertical foregrip with integral Picatinny rail and storage compartment | 080926-69114-8   | 69114          |       |
| Safety Wand   | Red              | 080926-74903-0 | 74903 |
| Safety Wand   | Yellow           | 080926-74904-7 | 74904 |
| Safety Wand   | Glow in the dark | 080926-74913-9 | 74913 |
| Flip Lens   | I/R              | 080926-74039-6 | 74039 |
| Flip Lens   | Red              | 080926-85115-3 | 85115 |
| Flip Lens   | Blue             | 080926-85116-0 | 85116 |
| Flip Lens   | Green            | 080926-85117-7 | 85117 |
| Tactical Holster  |                  | 080926-88051-1 | 88051 |
| Black nylon holster   |                  | 080926-85905-0 | 85905 |
| Black leather holster - plain   |                  | 080926-74059-4 | 74059 |
| Black leather holster - basket weave pattern  |                  | 080926-74060-0 | 74060 |

