

# Knucklehead® (Flood Model) Div. 2 Rechargeable Worklight

FL 1 STANDARD	HIGH	LOW
	200 LUMENS	63 LUMENS
	3h 30min	16h
	68m	37m
	1150cd	350cd

Flash runs 8 hours  
Moonlight mode runs 20 days



Head rotates 360°  
Articulates 210°



Powerful magnet is removeable. Includes a cover to protect painted surfaces



Integrated stowable hook

**Case** Housing, base and battery housing made from high impact super tough nylon offering exceptional durability. All openings are O-ring sealed for weather resistance. Circular rare-earth magnet surrounded by durable nickel plated steel housing. One-way valve for case venting. Available in high visibility yellow or black. Unbreakable polycarbonate lens with silicone anti-scratch coating assembled in a heavy duty bezel. O-ring sealed.

**Dimensions/** Height: 9.20 in. (23.4 cm)      Width: 2.85 in. (7.2 cm)      Thickness (at magnet): 2.75 in. (7.0 cm)  
**Weight:** Weight: NiCd: 23.1 oz (655 grams)\* Alkaline: 18.3 oz (519 grams)

**Light Source:** Two C4® LEDs, impervious to shock with a 50,000 hour lifetime. Dual wide pattern parabolic reflectors inset into larger textured reflector provide a smooth flood pattern for close-up work. Optimized electronics provide regulated intensity.

**On/Off:** Sonic welded push-button switch designed for extremely long life. Rubber dome push-button actuator provides easy operation even when wearing heavy gloves.

**Output/** 4 modes:  
**Run Time:**

- High for a soft flood beam to illuminate your work area: 200 lumens; 1,150 candela; runs 3.5 hours
- Low for light without the glare and longer run time: 63 lumens; 350 candela, runs 16 hours
- Moonlight for low-level lighting and extended run time (ideal for emergency situations): runs 20 days
- Flash for signaling: runs 8 hours

**Battery/** Industrial rechargeable NiCd battery can be recharged up to 1,000 times. Optional 4 "AA" alkaline non-rechargeable battery pack provides fast replacement with readily available batteries.

AC and DC one-hour fast chargers with full charge indicators designed specifically for AC or DC power sources.

Steady Charger, which requires up to 10 hours for a complete charge, can be used with 100V, 120V, 230V, 240V, or 12V DC power sources.

PiggyBack® charger allows for simultaneously charging of the Knucklehead and a spare battery so you always have a light when you need it.

**Features:**

- Dual C4 LED technology for extreme brightness
- Full 360 degree rotation head with 210 degrees of articulation.
- IPX4 water-resistant. All openings o-ring sealed
- 2 meter impact resistance tested.
- Removable magnet with 135 lb pull strength and integrated hook
- Serialized for positive identification.

**Approvals:** Class I, Division 2, Groups A,B,C,D; Class II, Division 2, Groups F,G; Class III, Temp Code: T4

Charger meets requirements of NFPA 1901-14.1.11.2 (2009) mounted in any position.

Meets applicable European Community Directives.

**Warranty:** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Part #	Description	UPC
<i>Without Charger</i>		
90601	Knucklehead - Black	080926-90601-3
90621	Knucklehead - Yellow	080926-90621-1
<i>Alkaline Model</i>		
90641	Knucklehead Alkaline Model - Black	080926-90641-9
90642	Knucklehead Alkaline Model - Yellow	080926-90642-6
<i>See reverse for additional configurations and part numbers</i>		

Assembled in USA



Part #	Description	UPC
<i>Steady Charge with AC/DC charger holders</i>		
90607	Knucklehead 120V AC/ DC - Black	080926-90607-5
90627	Knucklehead 120V AC & DC - Yellow	080926-90627-3
90608	Knucklehead 230V AC & DC - Black	080926-90608-2
90628	Knucklehead 230V AC & DC - Yellow	080926-90628-0
90609	Knucklehead 240V AC & DC - Black	080926-90609-9
90629	Knucklehead 240V AC & DC - Yellow	080926-90629-7
90610	Knucklehead 100V AC & DC - Black	080926-90610-5
90630	Knucklehead 100V AC & DC - Yellow	080926-90630-3
90602	Knucklehead 120V AC - Black	080926-90602-0
90622	Knucklehead 120V AC - Yellow	080926-90622-8
90603	Knucklehead 230V AC - Black	080926-90603-7
90623	Knucklehead 230V AC - Yellow	080926-90623-5
90604	Knucklehead 240V AC - Black	080926-90604-4
90624	Knucklehead 240V AC - Yellow	080926-90624-2
90605	Knucklehead 100V AC - Black	080926-90605-1
90625	Knucklehead 100V AC - Yellow	080926-90625-9
90606	Knucklehead 12V DC - Black	080926-90606-8
90626	Knucklehead 12V DC - Yellow	080926-90626-6
<i>Steady Charge PiggyBack</i>		
90613	Knucklehead 120V AC/DC PiggyBack - Black	080926-90613-6
90633	Knucklehead 120V AC/DC PiggyBack - Yellow	080926-90633-4
90634	Knucklehead 230V AC/DC PiggyBack - Yellow	080926-90634-1
90614	Knucklehead 230V AC/DC PiggyBack - Black	080926-90614-3
90615	Knucklehead 240V AC/DC PiggyBack - Black	080926-90615-0
90635	Knucklehead 240V AC/DC PiggyBack - Yellow	080926-90635-8
90616	Knucklehead 100V AC/DC PiggyBack - Black	080926-90616-7
90636	Knucklehead 100V AC/DC PiggyBack - Yellow	080926-90636-5
<i>Fast Charge</i>		
90611	Knucklehead 120V AC FC - Black	080926-90611-2
90631	Knucklehead 120V AC FC - Yellow	080926-90631-0
90612	Knucklehead 230V AV FC - Black	080926-90612-9
90632	Knucklehead 230V AC FC - Yellow	080926-90632-7
90620	Knucklehead 12V DC FC - Black	080926-90620-4
90640	Knucklehead 12V DC FC - Yellow	080926-90640-2
<i>Fast Charge PiggyBack</i>		
90618	Knucklehead 120V AC FC PiggyBack - Black	080926-90618-1
90638	Knucklehead 120V AC FC PiggyBack - Yellow	080926-90638-9

Part #	Item	UPC
22050	DC2 direct wire charge cord (All Rechargeables)	080926-22050-8
22051	DC1 Charge Cord (All Rechargeables)	080926-22051-5
22311	120V AC charge cord	080926-22311-0
22241	240V AC charge cord	080926-22241-0
22664	230V AC charge cord	080926-22664-7
2266	100V AC charge cord	080926-22666-1
90010	Steady Charge (SC) Plug-In Charger Holder**	080926-90010-3
90011	AC Fast Charger (Includes Holder)	080926-90011-0
90012	DC #1 Fast Charger (Includes Holder)	080926-90012-7
90013	DC #2 Fast Charger (Includes Holder)	080926-90013-4
90110	Steady Charge (SC) PiggyBack® Charger	080926-90110-0
90111	AC PiggyBack® Fast Charger	080926-90111-7
90112	DC #1 PiggyBack® Fast Charger	080926-90112-4
90113	DC #2 PiggyBack® Fast Charger	080926-90113-1
90130	Div 1 Battery Pack (Blue Sleeve, NiCd Battery)	080926-90130-8
90338	Div 2 Battery Pack (Black Sleeve, NiCd Battery)	080926-90338-8
90400	Bank Charger (SC) 120V AC	080926-90400-2
90401	Bank Charger 12V DC	080926-90401-9
90542	Alkaline battery pack (Batteries not included)	080926-90542-9

\*\*Cords not included



**STREAMLIGHT**



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax  
www.streamlight.com ©Streamlight Knucklehead Flood Model 5/14