

Waypoint® Lithium Ion Rechargeable Pistol Grip Spotlight

FL 1 STANDARD	HIGH	MEDIUM	LOW
	1000 LUMENS	550 LUMENS	35 LUMENS
	3h	6h	80h
	678m	490m	200m
	115,000 cd	60,000 cd	10,000 cd



Case Material: High impact polycarbonate housing. Unbreakable polycarbonate lens. O-ring sealed. Rubberized lens ring and cushioned-grip handle. Available in yellow and black

Dimensions/ Length: 6.75 in. (17.15 cm); Height: 7.14 in. (18.14 cm); Head Diameter: 3.62 in. (9.20 cm)
Weight: 1.52 lb (691 grams)

Light Source: C4® LED technology, shock-proof with a 50,000 hour lifetime.

Light Output: High: 1,000 lumens; 115,000 candela; 678m beam distance; runs 3 hours
Medium: 550 lumens; 60,000 candela; 490m beam distance; runs 6 hours
Low: 35 lumens; 10,000 candela; 200m beam distance; runs 80 hours
Deep-dish parabolic reflector produces a long range targeting beam with optimum peripheral illumination. Optimized electronics provide regulated intensity.

On/Off: Trigger style switch with momentary or click on/off operation. Secondary rotary switch selects output mode.

Battery: Lithium Ion with on-board safety control circuit, rechargeable up to 800 times

Features:

- LED Solid State power regulation provides maximum light output throughout battery life
- IPX8: Submersible. 2 meter submersion for a period of 30 minutes
- 1m impact resistance tested
- Integrated stand for hands-free scene lighting; removable lanyard
- Weight balanced design virtually eliminates user hand fatigue

Approvals: Most models meet applicable European Community Directives



CEC Compliant

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Go to www.streamlight.com/support for a complete copy of the warranty, and information on product registration and the location of authorized service centers. Retain your receipt for proof of purchase.



44918

Colored Filters:

- Help preserve night vision
- Constructed of flexible thermoplastic elastomer with polycarbonate lens
- For use with rechargeable Waypoint models
- Lightweight design won't weigh down the flashlight
- Fits securely fits over the head of the Waypoint



44916



44915



44923 - 12V DC Charge Cord



44909 - 120V AC Charge Cord



44919 - International AC Charge Cord

Item	UPC	Part #
Waypoint 120V AC with polymer holder/mount - Yellow	080926-44910-7	44910
Waypoint 120V AC with polymer holder/mount - Black	080926-44911-4	44911
Waypoint International with polymer holder/mount - Yellow	080926-44920-3	44920
Waypoint International with polymer holder/mount - Black	080926-44921-3	44921
Rechargeable 120V AC Charge Cord	080926-44909-1	44909
Rechargeable International AC Charge Cord	080926-44919-0	44919
Rechargeable 12V DC cord	080926-44923-7	44923
Waypoint (Rechargeable) Filter - Green	080926-44916-9	44916
Waypoint (Rechargeable) Filter - Red	080926-44915-2	44915
Waypoint (Rechargeable) polymer holder/mount	080926-44918-3	44918

Made in China



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight Waypoint Rechargeable 4/16