

# LiteBox® Rechargeable Lantern

Specific lighting needs require specific tools. With the right lighting tool, you can identify potential or existing problems before they interrupt your ability to get the job done. In addition the costs savings of using the right tool over time will benefit your bottom line.

There is a real need to cut costs wherever possible, yet we cannot afford to forget about environmental issues. Streamlight rechargeable lighting tools make good economic environmental sense. Over time they cost significantly less to operate; and they reduce the amount of batteries used, thereby relieving the problem of battery disposal. With Streamlight rechargeable flashlights, your plant will not only save on the cost of batteries, you'll save the time that's wasted when you discover your light isn't working and the steps involved in getting and replacing batteries. More powerful and more economical, Streamlight rechargeable lighting tools pack a lot of power, are very dependable and cost-efficient.

The rugged, dependable LiteBox was the first lantern with a swivel neck for full right angle lighting. It runs up to 9 hours and is now brighter than ever with an innovative new bulb configuration. The high-intensity halogen bi-pin bulb, available in spot or flood, provides a beam of up to 105,000 candela peak beam intensity. An optional xenon Dual Filament system is available, providing the security of a backup safety beam.

Case Material: High-impact ABS thermoplastic housing. Rubberized impact bumper, lens ring and cushioned-grip handle.

Dimensions/Weight: Length: 11.5 in. (29.2 cm) Width: 5.1 in. (13 cm) Height: 7 in. (17.8 cm) / 7.4 lbs (3.36 kg)\*

Light Source: High-intensity halogen bi-pin bulb available in 8 watt and 20 watt spot and flood PAR 36 assembly.

Light Output: Candela (Peak Beam Intensity) Bulb Lumens

<i>Bi-pin bulb:</i>		
8 watt flood	1,500	150
20 watt flood	3,000	400
8 watt spot	80,000	150
20 watt spot	105,000	400
<i>Dual Filament:</i>		
8 watt spot	70,000 each	157



Battery/Run Time: Zero-maintenance 6V, 12Ah sealed lead acid operates up to nine hours per charge and is rechargeable up to 500 times. Red & green LEDs give charge status feedback.

Models: Standard System - International safety orange or high-visibility yellow; includes shoulder strap; comes with AC and DC chargers and charge rack; ideal for field maintenance, inspection of construction sites, and remote equipment.

Vehicle Mount System - International safety orange or high-visibility yellow; comes with vehicle-mountable hard-wire rack and shoulder carrying strap.

Power Failure System - International safety orange or beige; includes AC/DC chargers and "smart" power failure circuitry that automatically goes on when the power goes off.

Dual Filament System - International safety orange or high visibility yellow; features backup 8 watt safety spot; includes shoulder strap.

Approvals\*\*: Most models meet applicable European Community Directives. Rack meets requirements of NFPA 1901-12-1.7 mounted in any position.

Warranty: Streamlight warrants this product to be free of defect for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work or that you manage to break as long as you own it. Of course, this limited lifetime warranty excludes abuse, batteries, bulbs and chargers. Rechargeable batteries and chargers have a one (1) year warranty with proof of purchase.

\*With battery (included in purchase).  
Assembled in USA

Item	UPC	Part #
Standard System - AC, 12V DC, shoulder strap & mounting rack		
LiteBox Standard System - 230V (8WS) - Yellow	080926-45121-6	45121
LiteBox Standard System - 240V (8WS) - Yellow	080926-45421-7	45421
LiteBox Standard System - 120V (8WS) - Yellow	080926-45117-9	45117
LiteBox Standard System - 100V (8WS) - Yellow	080926-45448-4	45448
LiteBox Standard System - 230V (20WS) - Yellow	080926-45122-3	45122
LiteBox Standard System - 240V (20WS) - Yellow	080926-45422-4	45422
LiteBox Standard System - 120V (20WS) - Yellow	080926-45109-4	45109
LiteBox Standard System - 100V (20WS) - Yellow	080926-45446-0	45446
LiteBox Standard System - 230V (20WF) - Yellow	080926-45120-9	45120
LiteBox Standard System - 240V (20WF) - Yellow	080926-45420-0	45420
LiteBox Standard System - 120V (20WF) - Yellow	080926-45113-1	45113

Item	UPC	Part #
Standard System - AC, 12V DC, shoulder strap & mounting rack		
LiteBox Standard System - 230V (8WS) - Orange	080926-45118-6	45118
LiteBox Standard System - 240V (8WS) - Orange	080926-45418-7	45418
LiteBox Standard System - 120V (8WS) - Orange	080926-45116-2	45116
LiteBox Standard System - 100V (8WS) - Orange	080926-45438-5	45438
LiteBox Standard System - 100V (8WS) - Yellow	080926-45437-8	45437
LiteBox Standard System - 230V (20WS) - Orange	080926-45123-0	45123
LiteBox Standard System - 240V (20WS) - Orange	080926-45423-1	45423
LiteBox Standard System - 120V (20WS) - Orange	080926-45110-0	45110
LiteBox Standard System - 100V (20WS) - Orange	080926-45435-4	45435
LiteBox Standard System - 230V (20WF) - Orange	080926-45112-4	45112
LiteBox Standard System - 240V (20WF) - Orange	080926-45412-5	45412
LiteBox Standard System - 120V (20WF) - Orange	080926-45111-7	45111
LiteBox Standard System - 100V (20WF) - Orange	080926-45447-7	45447
See reverse for additional part #s		





Item	UPC	Part #
Dual Filament Standard System AC/DC, shoulder strap & mounting rack		
Dual Filament Standard System - 230V (8WS) - Yellow	080926-45709-6	45709
Dual Filament Standard System - 240V (8WS) - Yellow	080926-45409-5	45409
Dual Filament Standard System - 120V (8WS) - Yellow	080926-45705-8	45705
Dual Filament Standard System - 230V (8WS) - Orange	080926-45708-9	45708
Dual Filament Standard System - 240V (8WS) - Orange	080926-45408-8	45408
Dual Filament Standard System - 120V (8WS) - Orange	080926-45704-1	45704
Dual Filament Standard System - 100V (8WS) - Orange	080926-45436-1	45436
Vehicle Mount System 12V DC, shoulder strap		
Vehicle Mount System - (8WS) - Yellow	080926-45108-7	45108
Vehicle Mount System - (20WS) - Yellow	080926-45104-9	45104
Vehicle Mount System - (8WS) - Orange	080926-45107-0	45107
Vehicle Mount System - (20WS) - Orange	080926-45102-5	45102
Dual Filament Vehicle Mount System 12V DC, shoulder strap		
Dual Filament Vehicle Mount System - (8WS) - Yellow	080926-45707-2	45707
Dual Filament Vehicle Mount System - (8WS) - Orange	080926-45706-5	45706
Power Failure System 230V AC, 12V DC chargers & mounting rack		
Power Failure System - 230V (8WS) - Orange	080926-45132-2	45132
Power Failure System - 240V (8WS) - Orange	080926-45432-3	45432
Power Failure System - 120V (8WS) - Orange	080926-45131-5	45131
Power Failure System - 230V (8WF) - Orange	080926-45128-5	45128
Power Failure System - 240V (8WF) - Orange	080926-45428-6	45428
Power Failure System - 120V (8WF) - Orange	080926-45127-8	45127
Power Failure System - 230V (8WS) - Beige	080926-45134-6	45134
Power Failure System - 240V (8WS) - Beige	080926-45434-7	45434
Power Failure System - 120V (8WS) - Beige	080926-45133-9	45133
Power Failure System - 230V (8WF) - Beige	080926-45130-8	45130
Power Failure System - 240V (8WF) - Beige	080926-45430-9	45430
Power Failure System - 120V (8WF) - Beige	080926-45129-2	45129

Item	UPC	Part #	
DC2 direct wire charge cord	080926-22050-8	22050	
DC1 Charge Cord	080926-22051-5	22051	
120V AC charge cord	080926-22311-0	22311	
240V AC charge cord	080926-22241-0	22241	
230V AC charge cord	080926-22664-7	22664	
100V AC charge cord	080926-22666-1	2266	
Locking Device (keyed differently) **Must be factory installed	080926-40163-1	40163	
Locking Device (keyed alike) **Must be factory installed	N/A	40164-525	
8 Watt Spot Lamp Assembly	080926-45911-3	45911	
Quick Release Strap	080926-44050-0	44050	
Shoulder Strap	080926-45232-9	45232	
Standard System Mounting Rack	Orange	080926-45070-7	45070
Direct Wire 12V DC Mounting Rack	Orange	080926-45071-4	45071
Standard System Mounting Rack	Yellow	080926-45072-1	45072
Direct Wire 12V DC Mounting Rack	Yellow	080926-45074-5	45074
Mounting Rack (LiteBox)	Beige	080926-45073-8	45073
20 Watt Bi-Pin Bulb (100 Hr)	080926-45902-1	45902	
8 Watt Bi-Pin Bulb (300 Hr)	080926-45903-8	45903	
8 Watt Flood Lamp Assembly	080926-45908-3	45908	
20 Watt Flood Lamp Assembly	080926-45910-6	45910	
8 Watt Spot Lamp Assembly	080926-45911-3	45911	
20 Watt Spot Lamp Assembly	080926-45913-7	45913	
8W Dual Filament Lamp Assembly	080926-45915-1	45915	
8 Watt Dual Filament Bulb	080926-45921-2	45921	
Sealed Lead Acid Battery	080926-45937-3	45937	
E-Spot Upgrade Kit	080926-45845-1	45845	
E-Flood Upgrade Kit	080926-45842-0	45842	

