





Strion LED HL® RECHARGEABLE FLASHLIGHT

FL 1 STANDARD	HIGH	MEDIUM	LOW
	500 LUMENS	250 LUMENS	125 LUMENS
	1h	2h	3h 30min
	200m	141m	100m
	10,000cd	5,000cd	2,500cd

Strobe runs 2.5 hours



Designed for maximum illumination

Case Material 6000 series machined aircraft aluminum with anodized finish

Dimensions Length: 5.90 in. (14.99 cm) Head Diameter: 1.25 in. (3.18 cm) Head Diameter at Tri-Lobe Anti-Roll Flange: 1.35 in. (3.43 cm) Barrel Diameter: 0.95 in. (2.41 cm)

Weight 5.2 oz (148 grams) with battery

Lens Borofloat high temperature glass lens

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime. Deep-dish parabolic reflector products a concentrated beam with optimal peripheral illumination

Switch Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

Output/Runtime: Three modes and strobe:

- High for a super-bright beam - 500 lumens; 10,000 candela peak beam intensity; 200 meter beam distance; runs 1 hour
- Medium for bright light and longer run times – 250 lumens; 5,000 candela peak beam intensity; 141 meter beam distance; runs 2 hours
- Low for light without glare and extended run times – 125 lumens; 2,500 candela peak beam intensity; 100 meter beam distance; runs 3.5 hours
- Strobe for disorienting or signaling your location; runs 2.5 hours

Battery Lithium Ion with on-board safety control circuit, 3.75V, 2200mAh, rechargeable up to 1000 times

Charging Clamp style charge holder with digital control circuit that prevents over charge. Fully recharges battery in 3 hours. Charge base LED indication: LED Steady – Charging; LED Blinking – Charged. Standard or PiggyBack® charger

- Features
- C4 LED technology for extreme brightness
 - LED Charge-continuity indicator on charger base; Compact, snap-in charger mounts in any position
 - IPX4 water resistant operation; 2 meter impact resistance tested
 - Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Assembled in USA

Item Description	UPC	Part #
Strion LED HL - 230V AC (Type C)/12V DC – 2 holders	080926-74761-6	74761
Strion LED HL - 240V AC/12V DC –2 holders	080926-74765-4	74765
Strion LED HL - IEC Type A (120V & 100V) AC/12V DC – 2 holders	080926-74752-4	74752
Strion LED HL - 230V AC (Type C)/12V DC – 1 holder	080926-74760-9	74760
Strion LED HL - 240V AC/12V DC – 1 holder	080926-74764-7	74764
Strion LED HL - IEC Type A (120V & 100V) AC/12V DC – 1 holder	080926-74751-7	74751
Strion LED HL - IEC Type A (120V & 100V) AC/12V DC – 1 holder Clam packaged	080926-74755-5	74755
Strion LED HL - 230V AC (Type C)	080926-74762-3	74762
Strion LED HL - 240V AC	080926-74766-1	74766
Strion LED HL - IEC Type A (120V & 100V) AC	080926-74753-1	74753
Strion LED HL with Grip Ring - IEC Type A (120V & 100V) AC	080926-74509-4	74509
Strion LED HL - 120V AC/12V DC PiggyBack	080926-74778-4	74778
Strion LED HL - 120V AC/12V DC PiggyBack - Kryptek®	080926-74395-3	74395
Strion LED HL - 12V DC	080926-74754-8	74754
Strion LED HL without Charger	080926-74750-0	74750
Strion LED HL without Charger - Kryptek	080926-74394-6	74394



All Rights Reserved. Kryptek® is a registered trademark of Kryptek Outdoor Group, LLC. Streamlight has not sought endorsement of this product from Kryptek Outdoor Group, LLC.



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
IEC Type A (100V & 120V) AC charge cord	080926-22060-7	22060
IEC Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
USB A to Micro (Custom)	080926-22070-6	22070
120V AC USB Wall Plug	080926-22058-4	22058
Intl AC USB Wall Plug	080926-22059-1	22059
6-unit Bank Charger 120V AC	080926-74400-4	74400
6-unit Bank Charger 230V AC	080926-74600-8	74600
6-unit Bank Charger 12V DC	080926-74401-1	74401
USB Charger Holder	080926-74114-0	74114
PiggyBack Charger Holder (cords and battery not included)	080926-74115-7	74115
Battery Stick (Li-Ion)	080926-74175-1	74175
Rail Mount	080926-74200-0	74200
Vertical Grip with Rail - machined aluminum, ambidextrous hard anodized rail grabber vertical foregrip with integral Picatinny rail and storage compartment	080926-69114-8	69114
Safety Wand Red	080926-74903-0	74903
Safety Wand Yellow	080926-74904-7	74904
Safety Wand Glow in the dark	080926-74913-9	74913
Flip Lens I/R	080926-74039-6	74039
Flip Lens Red	080926-85115-3	85115
Flip Lens Blue	080926-85116-0	85116
Flip Lens Green	080926-85117-7	85117
Tactical Holster	080926-88051-1	88051
Black nylon holster	080926-85905-0	85905
Black leather holster - plain	080926-74059-4	74059
Black leather holster - basket weave pattern	080926-74060-0	74060



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
 www.streamlight.com ©Streamlight, Inc. Strion LED HL 6/16