

Stinger DS LED HL® RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HIGH	MEDIUM	LOW
	640 LUMENS	340 LUMENS	170 LUMENS
	1h 15min	2h	4h
	297m	210m	148m
	22,000cd	11,000cd	5,500cd

Strobe runs for 3 hours



Designed for maximum illumination.

Material/ Lens 6000 series machined aircraft aluminum with non-slip rubberized comfort grip and anti-roll rubber ring. Unbreakable polycarbonate lens with scratch-resistant coating

Dims/Weight Length: 8.85 in. (22.48 cm) Major Diameter: 1.62 in. (4.11 cm); Body Diameter: 1.17 in. (2.97 cm) 12.8 oz (364 grams)

Light Source C4® LED technology, shock-proof with a 50,000 hour lifetime. Deep-dish parabolic reflector produces a concentrated beam with optimum peripheral illumination. Regulated run time provides consistent performance throughout battery life

Switch Dual switch technology - Access high, medium, low and strobe via the indepently working head mounted push-button switch or tail switch

Battery 3-cell,3.6 Volt NiMH sub-C battery, rechargeable up to 1000 times

Charging Ten hours to fully recharge on 100V, 120V, 230V or 240V AC, or 12V DC, 2.5-hour fast charger or PiggyBack® charger model available

Features

- Anti-roll ring included
- LED charge-continuity indicator, compact
- IPX4 Rated for water resistant operation
- 1 meter impact resistance tested
- Snap-in charger holder that mounts in any position
- Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item Description	UPC	Part #
Stinger DS LED HL w/230V AC/12V DC – 2 holders (NiMH)	080926-75464-5	75464
Stinger DS LED HL w/240V AC/12V DC –2 holders (NiMH)	080926-75472-0	75472
Stinger DS LED HL w/120V AC/12V DC – 2 holders (NiMH)	080926-75454-6	75454
Stinger DS LED HL w/100V AC/12V DC – 2 holders (NiMH)	080926-75459-1	75459
Stinger DS LED HL w/230V AC (NiMH)	080926-75466-9	75466
Stinger DS LED HL w/240V AC (NiMH)	080926-75473-7	75473
Stinger DS LED HL w/120V AC (NiMH)	080926-75455-3	75455
Stinger DS LED HL w/100V AC(NiMH)	080926-75460-7	75460
Stinger DS LED HL w/12V DC (NiMH)	080926-75456-0	75456

Item Description	UPC	Part #
Stinger DS LED HL w/230V AC/12V DC – 1 PiggyBack (NiMH)	080926-75471-3	75471
Stinger DS LED HL w/240V AC/12V DC – 1 PiggyBack (NiMH)	080926-75475-1	75475
Stinger DS LED HL w/120V AC/12V DC – 1 PiggyBack (NiMH)	080926-75458-4	75458
Stinger DS LED HL w/100V AC/12V DC – 1 PiggyBack (NiMH)	080926-75462-1	75462
Stinger DS LED HL w/230V AC/12V DC – FC 2 holders (NiMH)	080926-75469-0	75469
Stinger DS LED HL w/240V AC/12V DC – FC 2 holders (NiMH)	080926-75474-4	75474
Stinger DS LED HL w/120V AC/12V DC – FC 2 holders (NiMH)	080926-75457-7	75457
Stinger DS LED HL w/100V AC/12V DC – FC 2 holders (NiMH)	080926-75461-4	75461
Stinger DS LED HL without Charger (NiMH)	080926-75453-9	75453



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
5 Unit Bank Charger, 100V	080926-75700-4	75700
5 Unit bank charger 100V	080926-75701-1	75701
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
PiggyBack® Charger Holder Fast Charge & Battery	080926-75276-4	75276
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
Battery Stick (Lithium Ion)	080926-75176-7	75176

Item	UPC	Part #
Flip Lens	IR	080926-75027-2 75027
Flip Lens	Red	080926-75115-6 75115
Flip Lens	Blue	080926-75116-3 75116
Flip Lens	Green	080926-75117-0 75117
Safety Wand	Blue	080926-75902-2 75902
Safety Wand	Red	080926-75903-9 75903
Safety Wand	Yellow	080926-75904-6 75904
Safety Wand	White	080926-75908-4 75908
Safety Wand	Glow in the Dark	080926-75913-8 75913
Ring Holder		080926-75906-0 75906
Duty Holster		080926-88053-5 88053
Holster		080926-75927-5 75927
Loop holster		080926-75928-8 75928
Leather holster: Plain - Stinger LED/PolyStinger LED		080926-75133-0 75133
Leather holster: Basket Weave - Stinger LED/PolyStinger LED Series		080926-75134-7 75134