





# Stinger® HPL™ LONG-RANGE RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HIGH	MEDIUM	LOW
	<b>740</b> LUMENS	<b>380</b> LUMENS	<b>190</b> LUMENS
	<b>1h 15min</b>	<b>2h 30min</b>	<b>4h 30min</b>
	<b>438m</b>	<b>310m</b>	<b>219m</b>
	<b>48,000cd</b>	<b>24,000cd</b>	<b>12,000cd</b>

Strobe runs for 3 hours



Material/ Lens 6000 series machined aircraft aluminum with non-slip rubberized comfort grip. Unbreakable polycarbonate lens with scratch-resistant coating

Dims/Weight Length: 9.23 in. (23.44 cm); Body Diameter: 1.17 in. (2.97 cm); 13.6 oz (385 grams)

Output/ Four operating modes:

- Runtime:
- High for a high-lumen, far-reaching beam: 740 lumens; 48,000 candela; 438m beam; runs 1.25 hours
  - Medium for bright light and longer run time: 380 lumens; 24,000 candela; 310m beam; runs 2.5 hours
  - Low provides extended run times for when a less intense beam is desired: 190 lumens; 12,000 candela; 219m beam; runs 4.5 hours
  - Strobe for disorienting or signaling: runs 3 hours

Light Source C4® LED technology, shock-proof with a 50,000 hour lifetime. Deep-dish parabolic reflector produces a long range targeting beam with optimum peripheral illumination to aid in navigation. Optimized electronics provide regulated intensity.

Switch Multi-function, easy access head mounted push-button switch designed for extremely long life; tested at 1 million actuations

Battery 3-cell, 3.6 Volt Ni-MH sub-C battery, rechargeable up to 1000 times

Charging Ten hours to fully recharge on AC 12V DC, 2.5-hour fast charger or PiggyBack® charger model available

- Features
- IPX4 water-resistant
  - LED charge-continuity indicator, compact
  - 3 meter impact resistance tested
  - Snap-in charger holder that mounts in any position
  - Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. **THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW.** You may have other specific legal rights which vary by jurisdiction.

*Assembled in USA of US and foreign parts*

Item	UPC	Item #
Stinger HPL IEC Type C (230V) AC/12V DC	080926-75982-4	75982
Stinger HPL 240V AC/12V DC	080926-75779-0	75779
Stinger HPL 120V AC/12V DC	080926-75763-9	75763
Stinger HPL IEC Type A (100V) AC/12V DC	080926-75758-5	75758
Stinger HPL IEC Type C (230V) AC	080926-75981-7	75981
Stinger HPL 240V AC	080926-75778-3	75778
Stinger HPL 120V AC	080926-75761-5	75761
Stinger HPL IEC Type A (100V)	080926-75757-8	75757
Stinger HPL 12V DC	080926-75799-8	75799
Stinger HPL 120V AC/12V DC PiggyBack	080926-75782-0	75782
Stinger HPL 120V AC/12V DC Fast Charge	080926-75785-1	75785
Stinger HPL (WITHOUT CHARGER)	080926-75980-0	75980



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
IEC Type A (100V/120V) AC charge cord	080926-22666-1	22666
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
Battery Stick (Lithium Ion)	080926-75176-7	75176

Item	UPC	Part #
Flip Lens	IR	080926-75027-2 75027
Flip Lens	Red	080926-75115-6 75115
Flip Lens	Blue	080926-75116-3 75116
Flip Lens	Green	080926-75117-0 75117
Safety Wand	Blue	080926-75947-3 75947
Safety Wand	Red	080926-75946-6 75946
Safety Wand	Yellow	080926-75948-0 75948
Safety Wand	White	080926-75949-7 75949
Safety Wand	Glow in the Dark	080926-75950-3 75950
Ring Holder		080926-75906-0 75906
Duty Holster		080926-88053-5 88053
Holster		080926-75910-7 75910
Loop holster		080926-75928-8 75928



**STREAMLIGHT**



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax  
 www.streamlight.com ©Streamlight, Inc. Stinger HPL 12/15