





ProTac® 2AA Professional Tactical Light

FL1 STANDARD	HIGH	LOW
	155 LUMENS	11 LUMENS
	2h	36h
	115m	28m
	3,300cd	200cd

Strobe runs 4 hours



Case Material/Lens: 6000 Series machined aircraft aluminum with anodized finish. Tempered glass lens, o-ring sealed.

Dimensions/ Length: 6.14 in (15.60 cm) Major Diameter: 0.90 in. (2.29 cm) Barrel Diameter: 0.65 in. (1.65 cm)
Weight: 3.4 oz (96 grams) with batteries

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime

On/Off: Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

TEN-TAP® Programmable Switch: Allows the user to select one of three different programs. To change to the next program, starting from the "Off" position, tap the switch rapidly 9 times (within 0.4 seconds per tap) and hold it down the 10th time. Continue holding the switch until the light turns off (approximately 1 second), then release the switch.

Available programs: 1.) High-Strobe-Low (Factory Default) 2.) High Only 3.) Low-High

Battery: Two AA alkaline batteries (included)

- Features:
- LED Solid State Power Regulation provides maximum light output throughout battery life
 - IPX7 waterproof to 1 meter for 30 minutes
 - 2 meter impact resistance tested
 - TEN-TAP programmable switch allows user to select one of three different programs
 - Anti-roll facecap
 - Removable pocket clip
 - Serialized for positive identification
 - RoHS compliant

Approvals: Meets applicable European Community directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Visit www.streamlight.com for full warranty information.

Item	UPC	Part #
ProTac 2AA with white LED Black	080926-88033-7	88033
Nylon Holster - ProTac 2AA	080926-88038-2	88038

Made in China



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. ProTac 2AA 1/14