

SURVIVOR® RIGHT ANGLE FLASHLIGHT



Custom designed optic with optional, interchangeable Smoke-Cutter® plugs for preferred beam pattern:

- Black plug significantly reduces peripheral light for a tighter beam
- Amber plug reduces peripheral light and eye fatigue caused by glare

- Case** Housing, base and battery housing made from high impact super tough nylon offering exceptional durability. All openings are O-ring sealed for weather resistance.
- Material:** Spring loaded clip with built in D-ring easily attaches to belts and harnesses and reduces unwanted rotation. One way valve for case venting. Available in international safety orange, high visibility yellow or black
- Dimensions/** Height: 7.06 in. (17.92 cm); Height in charger: 8.67 in. (22.02 cm); Width: 2.85 in. (7.24 cm); Diameter: 2.87 in. (7.29 cm) Grip area: Height: 3.6 in. (9.14 cm); Thickness: 1.35 in. (3.43cm); Width: 2.20 in. (5.59 cm)
- Weight:** NiCd: 18.0 oz (510 grams) Alkaline: 13.7 oz (388 grams)
- Light** C4® LED technology, impervious to shock with a 50,000 hour lifetime
- Source:** Custom "Total Internal Reflection" optic for narrow beam and optimum peripheral illumination. Insertable black plug reduces peripheral illumination for improved smoke cutting ability or amber plug reduces eye fatigue.
- Four lighting modes:**
- High for a super-bright beam that pierces through smoke: 41,000 candela; 175 lumens; 405m beam distance; runs 3.5 hours (NiCd); runs 4 hours (alkaline)
 - Low for bright light and longer run time: 14,000 candela; 60 lumens; 237m beam distance; runs 13 hours (NiCd); runs 15 hours (alkaline)
 - Flash for signaling: runs 8 hours
 - Moonlight mode provides low-level lighting for battery conservation: runs 20 days
- On/Off:** Ultrasonic welded push button switch designed for extremely long life. Rubber dome push button actuator provides easy operation even when wearing heavy gloves.
- Battery:** Industrial rechargeable nickel-cadmium 4.8 volt, 1.8 amp hour, 4 cell sub-C rechargeable up to 1,000 times. Optional four "AA" alkaline battery pack provides fast replacement with readily available batteries.
- Charging:** AC and DC one-hour fast chargers with full charge indicators designed specifically for AC or DC power sources. Universal steady charger requires up to 10 hours for a complete charge, can be used with AC or 12V DC by exchanging its charge cord
- Features:**
- Reduced bezel length to minimize snag hazards
 - Updated clip design for easy attachment on turnout gear
 - IPX4 rated design; water resistant
 - 2 meter impact resistance tested.
- Approvals:** Class I, II, Division 1, Groups C, D, E, F, G; Class III, T-Code: T4
Class I, Division 2, Groups A, B, C, D; T-Code: T4
Charger meets requirements of NFPA 1901-14.1.11.2 (2003) mounted in any position
MSHA: Permissible Flashlight, Approval No. 20-A150001-0.
- Warranty:** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction

Item	UPC	Part #
Survivor - 230V AC (Type C)/ 12V DC cords - Yellow	080926-90515-3	90515
Survivor - 240V AC/12V DC cords - Yellow	080926-90516-0	90516
Survivor - 120V AC/12V DC cords - Yellow	080926-90513-9	90513
Survivor - IEC Type A (100V) AC/12V DC cords - Yellow	080926-90517-1	90517
Survivor - 230V AC (Type C)/ 12V DC cords - Orange	080926-90505-4	90505
Survivor - 240V AC/12V DC cords - Orange	080926-90506-1	90506
Survivor - 120V AC/12V DC cords - Orange	080926-90503-0	90503
Survivor - IEC Type A (100V) AC/12V DC cords - Orange	080926-90507-8	90507
Survivor - 230V AC (Type C)/ 12V DC cords - Black	080926-90525-2	90525
Survivor - 240V AC/12V DC cords - Black	080926-90526-9	90526
Survivor - 120V AC/12V DC cords - Black	080926-90523-8	90523
Survivor - IEC Type A (100V) AC/12V DC cords - Black	080926-90527-6	90527

Item	UPC	Part #
Survivor - 120V AC Fast Charge - Yellow	080926-90512-2	90512
Survivor - 120V AC Fast Charge - Orange	080926-90502-3	90502
Survivor - 120V AC Fast Charge - Black	080926-90522-1	90522
Survivor - 12V DC Fast Charge - Yellow	080926-90519-1	90519
Survivor - 12V DC Fast Charge - Black	080926-90528-3	90528
Survivor - 12V DC Fast Charge - Orange	080926-90509-2	90509
Survivor(WITHOUT CHARGER) - Yellow	080926-90510-8	90510
Survivor (WITHOUT CHARGER) - Orange	080926-90500-9	90500
Survivor (WITHOUT CHARGER) - Black	080926-90520-7	90520
Survivor Alkaline Model - Yellow	080926-90541-2	90541
Survivor Alkaline Model - Orange	080926-90540-5	90540
Survivor Alkaline Model - Black	080926-90545-0	90545

Assembled in USA



Item	UPC	Part #
DC2 direct wire charge cord (All Rechargeables)	080926-22050-8	22050
DC1 Charge Cord (All Rechargeables)	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
240V AC charge cord	080926-22241-0	22241
IEC Type C (230V) AC charge cord	080926-22061-4	22061
IEC Type A (100V/120V) AC charge cord	080926-22060-7	22060
Steady Charge (SC) Plug-In Charger Holder **Cords not included	080926-90010-3	90010
AC Fast Charger (Includes Holder)	080926-90011-0	90011
DC #1 Fast Charger (Includes Holder)	080926-90012-7	90012
DC #2 Fast Charger (Includes Holder)	080926-90013-4	90013
Steady Charge (SC) PiggyBack® Charger **Cords not included	080926-90110-0	90110
AC PiggyBack® Fast Charger	080926-90111-7	90111
DC #1 PiggyBack® Fast Charger	080926-90112-4	90112
DC #2 PiggyBack® Fast Charger	080926-90113-1	90113
Battery Pack Assembly (Blue Sleeve, NiCd Battery) Div 1	080926-90130-8	90130
Battery Pack Assembly (Black Sleeve, NiCd Battery) Div 2	080926-90338-8	90338
Bank Charger (SC) 120V AC	080926-90400-2	90400
Bank Charger (SC) 230V AC	080926-90600-6	90600
Bank Charger DC	080926-90401-9	90401
Survivor alkaline battery pack (Batteries not included)	080926-90542-9	90542

