

SEPTOR® LED HEADLAMP
ALKALINE AAA BATTERY-POWERED HEADLAMP

MARKET
APPLICATIONS: Professional Light - Hardware/Tool, Industrial, Automotive, Sporting Goods, Consumer, Emergency Medical Services, Safety, Pest Control, Boating, Aviation.

DESCRIPTION: The light weight Septor® headlamp with elastic adjustable head strap features (7) ultra bright 100,000 hour life white LEDs for wide task lighting and three power modes. It is also equipped with a low battery warning indicator.

CASE MATERIAL: Tough ABS thermoplastic plastic construction with elastomer over mold. Available in Yellow.

DIMENSIONS: Face Cap Diameter: 1.75 in. (4.45 cm)
 Maximum Width: 2.70 in. (6.85 cm)
 Maximum Depth: (Includes head strap mounting plate) 2.40 in. (6.09 cm)

WEIGHT: 5.50 oz (156.0 grams) with batteries (included with purchase).

LENS: Unbreakable polycarbonate lens.

LIGHT SOURCE: 100,000 hour life 5 mm LEDs

LIGHT OUTPUT: (7) LEDs - 120 Lumens, 900 candela peak beam intensity, and 60 meter beam distance.
 (3) LEDs - 45 Lumens, 375 candela peak beam intensity, and 35 meter beam distance.
 (1) LED - 13 Lumens, 100 candela peak beam intensity, and 20 meter beam distance.


ON/OFF: Push button switch - Sequences through (1) LED, (3) LEDs, (7) LEDs and Off.

RUN TIME: See chart for run time data. All runtime claims are to 10% of initial lumen output.

BATTERY: Three (3) "AAA" size, Alkaline batteries.

FEATURES:





 LED technology for extreme brightness.
 Low Battery Indicator - Red LED flashes when battery voltage is low and batteries are near the end of their usable life. LED is located in the reflector in between the "Low Batt" marking and functions while the light is energized.
 IPX4 rated for water resistant operation.
 2 meter impact resistance tested.
 90° tilting head.
 Rubber hard hat strap. (Included with purchase)

APPROVALS:  Class 1, Division 2, Groups A,B,C,D; Class II, Division 2, Groups F,G; Class III, Temp Code: T5

 Meets applicable European Community Directives.

WARRANTY: Streamlight's Limited Lifetime Warranty

OPTIONAL ACCESSORIES: N/A

	FL1 STANDARD	7 LEDs	3 LEDs	1 LED
OUTPUT		120 LUMENS	45 LUMENS	13 LUMENS
RUNTIME		3.5h	10h	55h
DISTANCE		60m	35m	20m
INTENSITY		900cd	375cd	100cd

