




PRODUCT FACT SHEET

STREAMLIGHT NANOLIGHT™ MINIATURE KEYCHAIN FLASHLIGHT

MARKET APPLICATIONS:	Consumer, Sporting Goods, Law Enforcement, Sporting Goods, Fire & Rescue, Hardware/Tool, Automotive, Industrial, Premium, Gift		
DESCRIPTION:	Truly tiny, the Nanolight™ is a weatherproof, personal flashlight featuring a 100,000 hour life LED. Includes a non-rotating snap hook for easy one handed operation when attached to a keychain. Batteries included.		
CASE MATERIAL:	Machined aircraft-grade aluminum with anodized finish. Available in black. LED available in white.		
DIMENSIONS:	Length: 1.47 in. (3.73 cm)	Diameter: Head Diameter: 0.51 in. (1.30 cm) Body Diameter: 0.43 in. (1.09 cm)	
WEIGHT:	0.36 oz (10 grams)*		
LIGHT SOURCE:	5mm white LED, impervious to shock with a 100,000 hour lifetime.		
LIGHT OUTPUT:	LED Rating: 10 Lumens typical. Parabolic shaped LED area optimizes beam performance.		
ON/OFF:	Rotating On/Off head switch.		
RUN TIME:	Up to 8 hours declining usable output.		
BATTERY:	Four (4) IEC-LR41 coin cells.		
APPROVALS**:	Most models meet applicable European Community Directives. 		
WARRANTY:	Limited lifetime warranty.		
OPTIONAL ACCESSORIES:	N/A		

* With battery (included in purchase)

Made in China

Document #156