

Fire Vulcan® Rechargeable Lantern



Case Material: High-impact ABS thermoplastic housing with rubberized cushioned-grip handle.

Dimensions/Weight: Length: 7.50 in. (19.05 cm) Width: 5 in. (12.70 cm) Height: 6.50 in. (16.51 cm) 3.3 lbs (1.5 kg) with battery

Light Source: High-intensity halogen bi-pin 8 watt spot with 100 hour life time, and two ultra bright Blue LEDs

Light Output/ 80,000 candela peak beam intensity ; 150 lumens

Run Time: Run times:

- o Steady Halogen and LEDs: Runs 3 hours
- o Blinking Halogen and LEDs: Runs 6 hours
- o LEDs only: Runs 60 hours

Battery: Zero-maintenance 4.5Ah sealed lead acid operates up to 3.25 hours per charge and is rechargeable up to 500 times. Red and green LEDs give charge status feedback

Models: **Standard System** - In high-visibility yellow or International safety orange. Includes shoulder strap; comes with AC and DC chargers and charging rack; ideal for field maintenance, inspection of construction sites and remote equipment

Vehicle Mount System - In high-visibility yellow or International safety orange, comes with vehicle-mountable hard-wire rack and shoulder carrying strap

- Approvals:
- USTC Class I, Div. 2, Grps. A,B,C,D T3; Class II, Div. 2, Grps. F,G; Class III T3C
 - Rack meets requirements of NFPA 1901-14.1.11.2 (2003) mounted in any position
 - Most models meet applicable European Community Directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item Description	UPC	Part #
Fire Vulcan Standard System - 230V AC/12V DC. (8WS) Orange	080926-44410-2	44410
Fire Vulcan Standard System - 230V AC/12V DC. (8WF) Orange	080926-44412-6	44412
Fire Vulcan Standard System - 240V AC/12V DC. (8WS) Orange	080926-44404-1	44403
Fire Vulcan Standard System - 100V AC/12V DC. (8WS) Orange	080926-44425-6	44425
Fire Vulcan Standard System - 120V AC/12V DC. (8WS) Orange	080926-44400-3	44400
Fire Vulcan Vehicle Mount System - 12V DC direct wire rack.(8WS) Orange	080926-44401-0	44401
Fire Vulcan Light Only (8WS) Orange	080926-44411-9	44411



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
240V AC charge cord	080926-22241-0	22241
230V AC charge cord	080926-22664-7	22664
100V AC charge cord	080926-22666-1	2266
Battery	080926-44007-4	44007
Quick Release Strap	080926-44050-0	44050
Charging Rack - Orange	080926-44101-9	44101
Direct Wire 12V DC Mounting Rack - Orange	080926-44131-6	44131
Shoulder Strap	080926-45232-9	45232

