

Makita®

18V X2 LXT® LITHIUM-ION CORDLESS CHAINSAW (TOOL ONLY)

POWERED BY TWO 18V LXT® LITHIUM-ION BATTERIES

- Makita-Built Motor Delivers 1,650 FPM for Increased Cutting Speed
- Two 18V LXT® Lithium-Ion Batteries Deliver the Power and Run Time for Corded Demands Without Leaving the 18V LXT® Platform
- Lower Noise Level at Only 89 dB(A) for Improved User Comfort
- 12" Guide Bar for Increased Capacity
- "Tool-Less" Chain Adjustments for Convenient Operation and Maintenance
- Front Hand Guard Engineered to Actuate Electric Brake When Engaged
- Zero Emissions and Reduced Maintenance, With No Need to Change Spark Plug, Clean Air Filter or Drain Fuel for Storage

Tool only - Batteries and charger not included

Model
HCU02ZX2

LXT
LITHIUM-ION

18V X2
36V

POWER



Makita-built motor delivers 1,650 FPM for increased cutting speed

INNOVATION



Two 18V LXT® Lithium-Ion batteries deliver the power and run time for corded demands

CONVENIENCE



"Tool-less" chain adjustments for convenient operation and maintenance

COMFORT

CORDLESS CHAINSAW

Noise level **89 dB(A)**

vs.

GAS CHAINSAW

Noise level **112 dB(A)**

Lower noise level at only 89 dB(A)

INCREASED CUTTING SPEED.

18V X2 LXT® LITHIUM-ION CORDLESS CHAINSAW (TOOL ONLY)

Model HCU02ZX2

FEATURES & BENEFITS

- Makita-built motor delivers 1,650 FPM for increased cutting speed
- Two LXT® Lithium-Ion batteries deliver the power and runtime for corded demands without leaving the 18V LXT® platform
- Lower noise level at only 89 dB(A) for improved user comfort
- 12" guide bar for increased capacity
- "Tool-less" chain adjustments for convenient operation and maintenance
- Zero emissions and reduced maintenance, with no need to change spark plug, clean air filter or drain fuel for storage
- Ergonomic top handle design with ergonomic grip engineered for the user to more easily apply even pressure when cutting; at 24-5/8" long and only weighs 11.2 lbs. (with batteries)
- Instant start-up: simply load two 18V LXT® batteries and the saw is ready to use
- Electric brake for maximum productivity
- Adjustable automatic chain lubrication with large oil reservoir
- Large oil filling port with view window allows operator to easily check bar oil level
- Retractable metal hook attaches to rope or harness for convenient transporting
- L.E.D. battery indicators show charge level for each 18V LXT® battery
- 30-minute rapid optimum charger communicates with the battery's built-in chip throughout the charging process to optimize battery life by actively controlling current, voltage and temperature
- 30-minute rapid optimum charger has a built-in fan to cool the battery to produce more lifetime work
- The charger earned the ENERGY STAR® label for meeting the strict energy-efficient guidelines set by the US Environmental Protection Agency (EPA) and US Department of Energy (DOE)
- 3-year warranty on tool and 1-year on battery and charger

SPECIFICATIONS

Guide bar length	12"
Chain speed	1,650 FPM
Chain pitch	3/8"
Chain gauge	0.043"
Voltage - Powered by 2 18V LXT® batteries	36V
Noise level	Under no load 89 dB(A)
	Under load 90 dB(A)
Net weight (w/2 18V LXT® batteries)	11.2 lbs.
Overall length	24-5/8"
UPC code	088381-643993

Makita offers a wide variety of CHAINSAW accessories. For a complete listing, please refer to the Makita General Catalog or visit our website at makitatools.com, or call 1-800-4MAKITA.

All specifications subject to change without prior notice. All models and accessories subject to stock on hand.
NTF-0413 MA-2039-13



Model HCU02ZX2



OPTIONAL ACCESSORIES

- 30-minute rapid optimum charger (DC18RC)
- 18V LXT® Lithium-Ion battery (BL1830-2)

STANDARD EQUIPMENT

- LXT® battery adaptor (BCV02)
- Chain (531-290-046)
- Guide bar (165245-8)
- Blade cover (419288-5)
- Chainsaw oil

Batteries and charger not included



Makita U.S.A., 14930 Northam St., La Mirada, CA 90638
"The Makita Teal color is the registered trade dress of Makita Corporation."