

# Swingout Mount for Flat-Panel Displays

### Model: AM175

Weight Capacity: 175 lb / 79.5 kg.

#### **Features**

1 Patented Griplates<sup>™</sup> (US Patent number 8,035,757 B2) support the flat-panel and holds the display tight on its mounting brackets

2 10° of tilt and up to 45° of swivel

3 Pull out arms extend 3.1 - 15.9 in. from the wall

- Combine with INW-AM325 in-wall box for a flush mount installation
- Scissor-style action pulls 15.9" from the wall
- Post-installation leveling enables fine-tune vertical adjustment after installation

The AM175 is a swingout mount for flat-panel displays up to 175 lb./79.5 kg. The AM175 allows up to 45° of swivel, 10° of tilt and extends 3.1 to 15.9 in. from the wall. The patented Griplates™ (US Patent number 8,035,757 B2) support the flat-panel and hold the display tight on its mounting brackets.







AM175 offers flat-panel displays 10° of tilt and 45° of swivel



Patented Griplates<sup>TM</sup> hold the display tight on its mounting brackets



Combine with the INW-AM325 in-wall box for a flush installation

# Swingout Mount for Flat-Panel Displays

#### Specifications

Weight

40.98 lb.| 18.6 kg

Width x Height x Depth

30.19 x 22.23 x 3.11-15.9 in. | 767 x 565 x 79-404 mm

Color Black

**Mounting Pattern** 

200 x 200 mm (Min) x 650 x 820 mm (Max)

**Total Weight Capacity** 

175 lb.| 79.5 kg

Warranty

Lifetime

#### Packaging

Width x Height x Depth

33.25 x 23.75 x 5 in. | 845 x 603 x 127 mm

**Contents** 

AM2 Swingout Arm (x1), Left Bracket (x1), Right Bracket (x1), Hardware Pack (x1), AM2 Extension Brackets (x2)

#### Accessories



in-wall box for the AM175 and AM300


INW-AM325



In-Wall A/V and Power GearBox™

**GB-INWAVP** 

## Architectural Drawing



Specifications subject to change without notice