


151-01667



**Article Number:** 151-01667

**Ratchet P Clamp, 1.38"-2.01" Bundle Dia., 90° Short Length, 0.256" Hole Dia., PA66HIRHSUV, Blk, 160/carton**

 **RoHS**

Base Data

<b>Local Order Number</b>	151-01667
<b>Type</b>	RCD90SM6
<b>Color</b>	Black (BK)
<b>Features and Benefits</b>	<ul style="list-style-type: none"><li>• One-piece ratchet closure design allows for easy installation during pre- or final assembly.</li><li>• Four sizes and multiple configurations handle a wide range of diameters and applications, reducing part inventory.</li><li>• Clamp interior is designed to guide and center bundle to reduce pinching.</li><li>• Easy release feature allows for quick adjustments and maintenance.</li><li>• Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.</li><li>• Steel mounting plate tolerates high torque mounting and is treated to resist chemicals and salt spray.</li><li>• Soft material inserts are available for sensitive bundles.</li><li>• For pre-determined clamp pressure, a Tension Tab is available for use with our EVO Series hand tools.</li></ul>
<b>Product Description</b>	The Ratchet P Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables by simply using a flat head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. The Ratchet P Clamp is offered in four sizes and in multiple mounting configurations.
<b>Short Description</b>	Ratchet P Clamp, 1.38"-2.01" Bundle Dia., 90° Short Length, 0.256" Hole Dia., PA66HIRHSUV, Blk, 160/carton

Product Dimensions

<b>Minimum Tensile Strength (Imperial)</b>	100.0 lbs
<b>Minimum Tensile Strength (Metric)</b>	445.0 N
<b>Length L (Imperial)</b>	6.58 "
<b>Length L (Metric)</b>	167.2 mm
<b>Length L2 (Imperial)</b>	3.49 "
<b>Length L2 (Metric)</b>	88.7 mm
<b>Variant</b>	90° Short
<b>Width W (Imperial)</b>	1.37 "
<b>Width W (Metric)</b>	34.9 mm
<b>Cable Tie Width Max. (Imperial)</b>	0.52
<b>Cable Tie Width Max. (Metric)</b>	13.2 mm
<b>Width W2 (Imperial)</b>	1.181 "
<b>Width W2 (Metric)</b>	30.0 mm
<b>Bundle Diameter Min. (Imperial)</b>	1.38 "
<b>Bundle Diameter Min. (Metric)</b>	35.1 mm
<b>Bundle Diameter Max. (Imperial)</b>	2.01 "
<b>Bundle Diameter Max. (Metric)</b>	51.0 mm

<b>Mounting Hole Diameter D (Imperial)</b>	0.256 "
<b>Mounting Hole Centers (Imperial)</b>	1.67 "

**Logistics and Packaging**

<b>Quantity Per</b>	bag
<b>Package Quantity</b>	160
<b>Package Quantity (Metric)</b>	160
<b>Carton Quantity</b>	160

**Material and Specifications**

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Compliant</b>	Yes
<b>Stamping Material</b>	Steel (ST)