



FGS-MSHS-F | 1147660

FiberGuide® Horizontal Straight Section, 4 in x 12 in, 6 ft length, yellow

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	300 mm x 100 mm 12 in x 4 in
Height	102.0 mm 4.0 in
Length	1829.0 mm 6.0 ft
Width	347.0 mm 13.7 in

Environmental Specifications

Flammability Rating	UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel LSZH TCO '99 WEEE
Safety Standard	UL

General Specifications

Product Feature	Solid
Product Type	Channel
Brand	FiberGuide®
Color	Yellow
Section Type	Straight section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant