

WRENCHES

ADJUSTABLE

Snap-on INDUSTRIAL BRANDS



ADJUSTABLE WRENCH WITH VALVE PERSUADER

Product Code	Length (Inches)	Maximum Jaw Opening (Inches)	Valve Wheel Wrench Opening
33HRUS	10	1 $\frac{3}{4}$	$\frac{3}{4}$

Features

- Two tools combined into one convenient operator's tool that can be used wherever valves are adjusted for flow and pressure
- 10" overall length supplies leverage while being compact enough to be easily carried.
- Big-mouth adjustable wrench has large, 1 $\frac{3}{4}$ " capacity.
- $\frac{3}{4}$ " valve wheel wrench opening.
- Precision hardened and anti-corrosion treated.
- Easy to read size measurement scale: fractional on one side, metric on the other



33 HR US



ADJUSTABLE WRENCH

Chrome Finish

Product Code	Length (Inches)	Maximum Jaw Opening (Inches)	Head Thickness (Inches)
AP-4A	4	$\frac{1}{2}$	$\frac{11}{32}$
AP-6A	6	$\frac{3}{4}$	$\frac{7}{16}$
AP-8A	8	1	$\frac{1}{2}$
AP-10A	10	1 $\frac{11}{64}$	$\frac{39}{64}$
AP-12A	12	1 $\frac{5}{16}$	$\frac{23}{32}$
AP-15A	15	1 $\frac{11}{16}$	$\frac{51}{64}$
AP-18A	18	2 $\frac{1}{16}$	$\frac{57}{64}$
AP-24A	24	2 $\frac{7}{16}$	1 $\frac{9}{64}$

Features

- Chrome plated finish allows for easy cleaning after each use.
- Serrated knurl is designed for quick and smooth adjustments.
- I-Beam designed handle provides strength and durability.
- Inch (SAE) scale is laser-etched on head face for easy determination of bolt head width.



AP-10A



ADJUSTABLE WRENCH

Black Finish

Product Code	Length (Inches)	Maximum Jaw Opening (Inches)	Head Thickness (Inches)
AB-4A	4	$\frac{1}{2}$	$\frac{11}{32}$
AB-6A	6	$\frac{3}{4}$	$\frac{7}{16}$
AB-8A	8	1	$\frac{1}{2}$
AB-10A	10	1 $\frac{11}{64}$	$\frac{39}{64}$
AB-12A	12	1 $\frac{5}{16}$	$\frac{23}{32}$
AB-15A	15	1 $\frac{11}{16}$	$\frac{51}{64}$
AB-18A	18	2 $\frac{1}{16}$	$\frac{57}{64}$
AB-24A	24	2 $\frac{7}{16}$	1 $\frac{9}{64}$

Features

- Drop forged, heat treated industrial finish with satin finish handles for firm safe grip.
- Inch (SAE) scale is laser-etched on head face for easy determination of bolt head width.



AB-10A

