

WILLIAMS®



3/8" DRIVE SHALLOW SOCKETS, 4 & 8 POINT, SAE

High-Polished Chrome Finish



BD-814



WSBD-7RC

		A	B	C	D	E		F
Product Code	Size (Inches)	OAL (Inches)	Drive End Diameter (Inches)	Working End Diameter (Inches)	Broach Depth (Inches)	Bolt Clearance Depth (Inches)	Bolt Clearance Diameter (Inches)	Nose Length (Inches)
BD-808	1/4	29/32	21/32	15/32	7/32	13/32	5/32	7/16
B-409 **	9/32	1 1/32	11/16	9/16	5/16	17/32	3/16	1/2
BD-810	5/16	29/32	21/32	9/16	1/4	13/32	1/4	7/16
BD-812	3/8	15/16	11/16	41/64	9/32	7/16	5/16	15/32
BD-814	7/16	1	23/32	23/32	9/32	1/2	5/16	-
BD-816	1/2	1	29/32	29/32	5/16	1/2	13/32	-
BD-818	9/16	1 1/8	1	1	13/32	5/8	17/32	-
BD-820	3/4	1 1/8	1 1/16	1 1/16	7/16	5/8	19/32	-

** 4 Point Socket
Fed. Spec: ANSI B107.1

WSBD-7RC 7 Piece 8 Point Socket Set on Clip Rail

Contents Include:

Product Code	Size (Inches)	Product Code	Size (Inches)	Product Code	Size (Inches)
BD-808	1/4	BD-814	7/16	BD-820	5/8
BD-810	5/16	BD-816	1/2		
BD-812	3/8	BD-818	9/16		

Features

- SUPERTORQUE® lobular openings for greater turning power without deforming the fastener.
- 8 point sockets are designed for quick engagement on 4 point fasteners.



WILLIAMS®

3/8" DRIVE 5 POINT PENTA-SOCKET

Black Industrial Finish



BB-526

		A	B	C	D	E	F	
Product Code	Size (Inches)	OAL (Inches)	Drive End Diameter (Inches)	Working End Diameter (Inches)	Broach Depth (Inches)	Bolt Clearance Depth (Inches)	Bolt Clearance Diameter (Inches)	Nose Length (Inches)
BB-526	$\frac{51}{64}$	1 $\frac{1}{16}$	1 $\frac{1}{8}$	1 $\frac{1}{8}$	$\frac{7}{16}$	$\frac{1}{2}$	$\frac{23}{32}$	-

Features

- 5 point Penta-Socket services 5 point nuts found on tamper-resistant Buffalo covers used by gas, electric, and some water companies to protect shutoff gates.



WILLIAMS®

3/8" DRIVE UNIVERSAL SOCKETS, 12 POINT, SAE

High-Polished Chrome Finish



BU-1220, BU-1212

		A	B	C	D	E	F	
Product Code	Size (Inches)	OAL (Inches)	Drive End Diameter (Inches)	Open End Diameter (Inches)	Broach Depth (Inches)	Bolt Clearance Depth (Inches)	Bolt Clearance Diameter (Inches)	Nose Length (Inches)
BU-1212	3/8	1 ²⁵ / ₃₂	3/4	1/2	1/4	1/2	5/16	15/64
BU-1214	7/16	1 ²⁵ / ₃₂	3/4	5/8	1/4	1/2	11/32	15/64
BU-1216	1/2	1 ²⁵ / ₃₂	3/4	11/16	5/16	9/16	11/32	9/32
BU-1218	9/16	1 ²⁵ / ₃₂	3/4	3/4	11/32	5/8	11/32	17/32
BU-1220	5/8	1 ²⁵ / ₃₂	3/4	7/8	13/32	11/16	11/32	17/32
BU-1222	11/16	2	3/4	15/16	7/16	23/32	11/32	17/32
BU-1224	3/4	2 1/8	3/4	1	17/32	13/16	11/32	5/8

Fed. Spec: ANSI B107.1

WSB-7U 7 Piece 12 Point Universal Socket Set on Clip Rail

Contents Include:

Product Code	Size (Inches)	Product Code	Size (Inches)	Product Code	Size (Inches)
BU-1212	3/8	BU-1218	9/16	BU-1224	3/4
BU-1214	7/16	BU-1220	5/8		
BU-1216	1/2	BU-1222	11/16		

Features

- Ideal for work in confined areas where fastener is inaccessible to standard sockets.



WSB-7U