

# PLIERS, CLAMPS & PIPE TOOLS

## WIRE TWISTER/CABLE CUTTER

**Snap-on** INDUSTRIAL BRANDS

**WILLIAMS**

### WIRE TWISTER / CUTTER

**Produces Right Hand (clockwise) Twists**

Product Code	Overall Length (Inches)	Jaw Length (Inches)	Cutting Blade Length (Inches)
WTC-11	8.5	1 1/16	1/4



#### Features

- Diamond-shaped, flat top jaw serrations hold wire firmly and resist knicking material being worked on.
- Diagonal nose configurations & "mini" frame allows access in tight quarters.
- Automatic return feature retracts automatically, speeding up operation use and reducing operator fatigue.
- Heat-treated cutting edge holds it edge for cutting tough (up to .041) stainless steel and safety wire.
- One hand operation allows for operator closing and locking with minimum of handle force.
- High carbon alloy steel forging are used for maximum durability and long life.



WTC-11



### CABLE CUTTER FOR FERROUS MATERIALS

**With Rubber Grips**

Product Code	Overall Length (Inches)	Cable Cutting Capacity (Inches)	Replacement Blade Kit
2520	22 1/2	1 3/16 Aluminum/Copper with 1/4 Messenger Wire	2520-SH

#### Features

- Lightweight handles provide ease of control while offering solid durability.
- Rubber grips offer control and comfort during working application.
- Cutting notch below top cutting blades provided for cuts on ferrous material.
- Replacement blade kit includes blades, screws, and nuts.



2520



### CABLE CUTTER FOR NON-FERROUS MATERIALS

**With Rubber Grips**

Product Code	Overall Length (Inches)	Cable Cutting Capacity (Inches)
2620-80	31 1/2	1 5/8 Aluminum/Copper

#### Features

- For non-ferrous material cutting only.
- Lightweight handles provide ease of control while offering solid durability.
- Rubber grips offer control and comfort during working application.
- Replacement blade kit includes blades, screws, and nuts.



2620-80

