

AXIS Camera Station S2016 Appliance

All-in-one recorder with integrated switch for high-definition surveillance

AXIS Camera Station S2016 is an out-of-the-box ready compact surveillance appliance with an integrated manageable PoE switch. AXIS S2016 is validated for reliable high-definition surveillance up to 4K. It is preloaded with AXIS Camera Station video management software with Universal licenses for 16 channels and other necessary system software. It is preconfigured to minimize installation time. AXIS S2016 has validated hardware components and three-year hardware warranty. AXIS Camera Station offers an intuitive user interface and allows users to take full advantage of Axis' wide range of video surveillance cameras and other IP products. It also supports integration of third-party cameras.

- > **All-in-one solution with integrated PoE switch**
- > **Validated with extensive support**
- > **High-definition surveillance up to 4K**
- > **AXIS Camera Station included**
- > **Full compatibility with Axis' products**



AXIS Camera Station S2016 Appliance

Licenses	16 AXIS Camera Station Universal licenses included.	Connectors	16x PoE ports RJ-45 10Base-T/100Base-TX, 2x switch uplink ports RJ-45/SFP 100Base-TX, 2x server LAN ports RJ-45/SFP 100Base-TX, 2x USB 2.0, 2x USB 3.0, 1x VGA, 1xHDMI 1.4b, 1x eSATA
Processor	Intel i5-4590S, 3,0GHz, 6MB Cache, 4C/4T, turbo	Operating conditions	0 °C to 40 °C (32 °F to 104°F)
Memory	UDIMM 8GB (1x8GB) 1600 MHz DDR3, non ECC	Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Storage	8 TB (2x4 TB) Surveillance Class HDD SATA 6Gb/s. Possible to add 2 additional HDD Boot drive 120 GB mSATA	Approvals	EN/IEC/UL 60950-1, FCC part 15 class A, VCCI class A, EN 55022 class A, ICES-3(A)/NMB-3(A), RCM AS/NZS CISPR 22 Class A, EN 55024, EN/IEC 61000-3-2, EN/IEC 61000-3-3
Switch	16 ports integrated, 277 W total power budget, Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 2 up to Class 4	Dimensions	538 x 438 x 44 mm (21.2 x 17.2 x 1.75 in)
Graphic card	Intel HD Graphics 4600 with Quick Sync Video	Weight	10 kg (22 lb)
Operating system	Microsoft Windows 10 IoT Enterprise	Included accessories	Rack mounting brackets, Installation guide, Power cable
Video streaming	Live view: Capable of 25 camera split views or 1 x 4K camera view Playback: 4 x 1080p camera split views or 1 x 4K camera view 2 screens supported.	Optional accessories	AXIS Camera Station S9001 MkII Desktop Terminal AXIS Camera Station S9002 Desktop Terminal AXIS T8310 Video Surveillance Control Board AXIS P8221 I/O Audio Module AXIS A1001 Network Door Controller
Recording	Qualified for recording with a total recording rate of 256 Mbit per second.	Warranty	Axis 3-year warranty, see www.axis.com/warranty
General			
Power	Max 500 W, 100 V AC to 240 V AC 277 W PoE dedicated		

AXIS Camera Station

For details about AXIS Camera Station features and functions please see Data Sheet on www.axis.com

Environmental responsibility:

www.axis.com/environmental-responsibility