

# AXIS Camera Station S2024 Appliance

All-in-one recorder with integrated switch for high-definition surveillance

AXIS Camera Station S2024 is an out-of-the-box ready compact surveillance appliance with an integrated manageable PoE switch. AXIS S2024 is validated for reliable high-definition surveillance up to 4K. It is preloaded with AXIS Camera Station video management software with Universal licenses for 24 channels and other necessary system software. It is preconfigured to minimize installation time. AXIS S2024 has validated hardware components and three-year hardware warranty. AXIS Camera Station offers an intuitive user interface and allows users to take full advantage of Axis' wide range of video surveillance cameras and other IP products. It also supports integration of third-party cameras.

- > **All-in-one solution with integrated PoE switch**
- > **Validated with extensive support**
- > **High-definition surveillance up to 4K**
- > **AXIS Camera Station included**
- > **Full compatibility with Axis' products**



## AXIS Camera Station S2024 Appliance

<b>Licenses</b>	24 AXIS Camera Station Universal licenses included.		2x USB 2.0, 2x USB 3.0, 1x VGA, 1xHDMI, 1x eSATA,
<b>Processor</b>	Intel i7-4790S, 3,2GHz, 8MB Cache, 4C/8T, turbo	<b>Operating conditions</b>	0 °C to 40 °C (32 °F to 104°F)
<b>Memory</b>	UDIMM 8GB (1x8GB) 1600 MHz DDR3, non ECC	<b>Storage conditions</b>	-40 °C to 65 °C (-40 °F to 149 °F)
<b>Storage</b>	12 TB (3x4 TB) Surveillance Class HDD SATA 6Gb/s. Possible to add 1 additional HDD Boot drive 120 GB mSATA <sup>a</sup>	<b>Approvals</b>	EN/IEC/UL 60950-1, FCC part 15 class A, VCCI class A, EN 55022 class A, ICES-3(A)/NMB-3(A), RCM AS/NZS CISPR 22 Class A, EN 55024, EN/IEC 61000-3-2, EN/IEC 61000-3-3
<b>Switch</b>	24 ports integrated, 277 W total power budget, Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 2 up to Class 4	<b>Dimensions</b>	538 x 438 x 44 mm (21.2 x 17.2 x 1.75 in)
<b>Graphic card</b>	Intel HD Graphics 4600 with Quick Sync Video	<b>Weight</b>	10 kg (22 lb)
<b>Operating system</b>	Microsoft Windows 10 IoT Enterprise	<b>Included accessories</b>	Rack mounting brackets, Installation guide, Power cable
<b>Video streaming</b>	<b>Live view:</b> Capable of 25 camera split views or 1 x 4K camera view <b>Playback:</b> 4 x 1080p camera split views or 1 x 4K camera view 2 screens supported.	<b>Optional accessories</b>	AXIS Camera Station S9001 MkII Desktop Terminal AXIS Camera Station S9002 Desktop Terminal AXIS T8310 Video Surveillance Control Board AXIS P8221 I/O Audio Module AXIS A1001 Network Door Controller
<b>Recording</b>	Qualified for recording with a total recording rate of 384 Mbit per second.	<b>Warranty</b>	Axis 3-year warranty, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>
<b>General</b>			
<b>Power</b>	Max 500 W, 100 V AC to 240 V AC 277 W PoE dedicated	a. For more info <a href="http://www.axis.com/support">www.axis.com/support</a>	
<b>Connectors</b>	24x PoE ports RJ-45 10Base-T/100Base-TX, 2x switch uplink ports RJ-45/SFP 100Base-TX, 2x server LAN ports RJ-45/SFP 100Base-TX		

## AXIS Camera Station

For details about AXIS Camera Station features and functions please see Data Sheet on [www.axis.com](http://www.axis.com)

Environmental responsibility:

[www.axis.com/environmental-responsibility](http://www.axis.com/environmental-responsibility)