

Security/Alarm/Access Control/Sound Low-voltage Cable Non-Shielded Plenum

Product Description

- FRPVC
- Bare Copper Conductor
- UL Listed Type CMP, CL3P

Applications

- For use in security systems, intercom systems, sound/audio systems, access control, power-limited controls.



Specification

- CONDUCTOR: Bare copper
- INSULATION: Polyvinyl Chloride (PVC)
- JACKET: Polyvinyl Chloride (PVC), White
- STANDARDS: NEC: CMP (22-16 AWG), CL3P (14-12 AWG)
- TEMPERATURE: 75°C

Standard color is white, other colors available. Most items available on spools or boxes except on larger O.D. products. Diameters and weights may vary among manufacturers. Paired conductors also available

<u>Part No.</u>	<u>Conductor Size AWG</u>	<u>No. of Conductors</u>	<u>Rating</u>	<u>Insulation</u>	<u>Insulation Thickness (in.)</u>	<u>Overall Jacket Thickness (in.)</u>	<u>Nom. O.D. (in.)</u>	<u>Approx. Wt. lb./1,000 ft.</u>
AL-2202C-1-2N-01	22 (SOL)	2	CMP	PVC	0.007	0.015	0.122	8
AL-2202C-2-2N-01	22	2	CMP	PVC	0.007	0.015	0.12	11
AL-2203C-2-2N-01	22	3	CMP	PVC	0.007	0.015	0.131	14
AL-2204C-2-2N-01	22	4	CMP	PVC	0.007	0.015	0.142	16
AL-2204C-1-2N-01	22 (SOL)	4	CMP	PVC	0.007	0.015	0.135	14
AL-2206C-2-2N-01	22	6	CMP	PVC	0.007	0.015	0.17	24
AL-2208C-2-2N-01	22	8	CMP	PVC	0.007	0.018	0.19	31
AL-2210C-2-2N-01	22	10	CMP	PVC	0.007	0.02	0.21	39
AL-2212C-2-2N-01	22	12	CMP	PVC	0.007	0.022	0.229	15
AL-2002C-2-2N-01	20	2	CMP	PVC	0.008	0.015	0.148	21

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

<u>Part No.</u>	<u>Conductor Size AWG</u>	<u>No. of Conductors</u>	<u>Rating</u>	<u>Insulation</u>	<u>Insulation Thickness (in.)</u>	<u>Overall Jacket Thickness (in.)</u>	<u>Nom. O.D. (in.)</u>	<u>Approx. Wt. lb./1,000 ft.</u>
AL-2003C-2-2N-01	20	3	CMP	PVC	0.01	0.015	0.161	26
AL-2004C-2-2N-01	20	4	CMP	PVC	0.01	0.018	0.178	26
AL-1802C-2-2N-01	18	2	CMP	PVC	0.009	0.015	0.172	16
AL-1803C-2-2N-01	18	3	CMP	PVC	0.009	0.015	0.187	30
AL-1804C-2-2N-01	18	4	CMP	PVC	0.009	0.018	0.203	37
AL-1806C-2-2N-01	18	6	CMP	PVC	0.009	0.02	0.226	52
AL-1808C-2-2N-01	18	8	CMP	PVC	0.009	0.02	0.242	66
AL-1602C-2-2N-01	16	2	CMP	PVC	0.009	0.018	0.198	30
AL-1604C-2-2N-01	16	4	CMP	PVC	0.009	0.02	0.234	54
AL-1402C-2-2N-01	14	2	CL3P	PVC	0.01	0.025	0.238	45
AL-1404C-2-2N-01	14	4	CL3P	PVC	0.01	0.025	0.286	74
AL-1202C-2-2N-01	12	2	CL3P	PVC	0.011	0.028	0.296	68

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.