Product Specifications





6-64 | 334-3 | MP-44U-F- | Modular Plug, 4P/4C, Unshielded, Flat Oval, 100 pcs

Body Features

Conductor Type Solid | Stranded

Configuration Features

Number of Positions 4
Keyed No

Contact Features

Contact Base Material Phosphor bronze

Contact Mating Area Plating Material Gold

Contact Mating Area Plating Thickness 50.00 µin | 1.27 µm

Number of Contacts Loaded 4

Dimensions

Cable Jacket Outside Diameter Range 0.09–0.19 in | 2.29–4.83 mm

Conductor Outside Diameter 0.034–0.039 in | 0.86–0.99 mm

Conductor Wire Size 26–24 AWG

Housing Features

Housing Material Glass filled polycarbonate

Industry Standards

UL Flammability Rating UL 1863

Packaging Features

Packaging Quantity 100

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Cable Type Flat oval, unshielded

Performance Category Category 3
Connector Style Plug
Jack Type RJ11

Product Specifications



6-641334-3 | MP-44U-F-1

Latch Style Standard
Product Type Connector

Shielded No

Termination Features

Termination Method to Wire/Cable Insulation Displacement Crimp (IDC)