



6-641337-2 | MP-66U-F-5
Modular Plug, 6P/6C, Unshielded, Flat Oval, 500 pcs

Body Features

Conductor Type	Solid Stranded
----------------	------------------

Configuration Features

Number of Positions	6
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm
Number of Contacts Loaded	6

Dimensions

Cable Jacket Outside Diameter Range	0.09–0.26 in 2.29–6.61 mm
Conductor Outside Diameter	0.034–0.039 in 0.86–0.99 mm
Conductor Wire Size	26–24 AWG

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

Packaging Features

Packaging Quantity	500
--------------------	-----

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Cable Type	Flat oval, unshielded
Performance Category	Category 3
Connector Style	Plug
Jack Type	RJ11
Latch Style	Standard

6-641337-2 | MP-66UF-5

Product Type	Connector
Shielded	No

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------